


## 7-Port USB 2.0 Hub

MODEL NUMBER: **U223-007**



### Description

The U223-007 7-port USB 2.0 hub allows you to connect up to seven USB devices to a single USB port on your computer. This unit meets or exceeds USB 2.0 specifications for data transmission rates up to 480 Mbps. Perfect for both the mobile and desktop user. While the hub will function in virtually all cases without needing external power, a compact multi-voltage AC adapter (110/220V) has been provided for the rare circumstance when connecting a power-hungry device. This device is backwards compatible so that it will function with both USB 2.0 and USB 1.1 devices. Over-current protection safeguards connected equipment from overvoltages.

### Features

- USB2.0 7-Port Hub
- Supports data transfer rates up to 480Mbps
- Connect up to 7 USB devices to a single USB port on your computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Per-port overcurrent protection
- Bus-powered or self-powered
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- The included external power supply provides 2A of power, to be shared between the hub ports (up to 500mA per port)
- Compact, multi-voltage power supply (110/220V) provided
- Compatible with all major operating systems

### Highlights

- Connects up to 7 USB 2.0 devices
- Bus-powered or optional AC adapter
- Compatible with all major operating systems

### System Requirements

- USB 2.0 Computer Port
- USB Peripherals

### Package Includes

- U223-007 USB 2.0 Hub
- User's Manual
- USB 2.0 Mini B male to USB 2.0 A male cable
- 5V/2A DC Power Supply Optional
- External Power Supply with 1-15P Plug (Input: 100-240V, 50/60Hz, 0.4A Max / Output: 5.0V, 2000mA)

## Specifications

### OVERVIEW

UPC Code	037332185389
Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
<b>VIDEO</b>	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(7) USB A (FEMALE)
Data Ports Details	(7) USB-A - USB 2.0
<b>INPUT</b>	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.4A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4
AC Power Adapter Cord Length (m)	1.2
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	6.53
Product Length (cm.)	16.6
Product Length (ft.)	0.544
Product Length (m)	0.166
<b>POWER</b>	
Power Source Type	AC Adapter
DC Barrel Plug	OD: 3.5 x 1.35 x 8mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	0.3
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power)
<b>PHYSICAL</b>	
Color	Black

Material of Construction	ABS
Included Mounting Accessories	No
Shipping Dimensions (hwd / in.)	2.10 x 3.10 x 7.50
Shipping Weight (lbs.)	0.70
Unit Dimensions (hwd / in.)	0.600 x 6.500 x 1.300
Unit Dimensions (hwd / cm)	16.6 x 3.33 x 1.6
Unit Packaging Type	Box
Unit Weight (lbs.)	0.14
Unit Weight (kg)	0.06
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 194°F (-10° to 90°C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	1 BTU/Hr
Power Provided to Connected Device(s)	5V 0.5A (2.5W) Output per USB port
<b>CONNECTIONS</b>	
Number of Ports	7
Side A - Connector 1	USB MINI-B 5-PIN (FEMALE)
Side B - Connector 1	(7) USB A (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	7
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
External Power Supply Certifications	DOE; FCC; UL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.