

Virtual 7.1-Channel USB External Sound Card

MODEL NUMBER: U237-001



Adds external microphone, speaker and/or headphone ports, as well as volume and mute controls, to your computer or laptop via USB port. An inexpensive replacement for damaged sound cards or audio connectors.

Description

The U237-001 Virtual 7.1-Channel USB External Sound Card plugs into your computer or laptop's USB port to provide easy-to-access audio-in and audio-out ports. A convenient, inexpensive replacement for a damaged sound card or audio connectors, the U237-001 lets you plug a microphone, speakers and/or headphones into its 3.5 mm audio jacks and enjoy rich, vibrant sound. By installing the Xear™ 3D Virtual 7.1-Channel Surround Sound software (included), you'll be able to customize the audio settings. In addition to the two audio ports, the U237-001 features volume controls, microphone and speaker muting buttons, and LEDs that indicate audio status, activity and microphone/speaker mute. It's plug-and-play, with the USB audio driver automatically installing upon connection to a USB port. Compatible with Windows® 2000™ and later, Mac OS X® and Linux. Xear 3D software compatible with Windows XP, 7 and 8™.

Features

Adds an External Sound Card to Your Computer's USB Port Dual 3.5 mm audio jacks for connecting microphone, speakers and/or headphones
 Inexpensive replacement for damaged sound card or audio connectors
 Easy-access volume controls
 Microphone/speaker muting buttons
 LEDs indicate status, activity and mute

Xear 3D Virtual 7.1-Channel Surround Sound Software Customizable audio settings
 Supports 3D and virtual 7.1-channel surround sound
 Preset sound effects with 10-band equalizer
 Software compatible with Windows XP, 7 and 8

Easy to Use Plug and play—no external power supply required
 USB driver automatically installs upon connection
 Unit compatible with Windows 2000 and later, Mac OS X and Linux

Specifications

OVERVIEW	
UPC Code	037332192745
Technology	Stereo Audio; USB 2.0 (High Speed)

Highlights

- Customizable audio settings via included CD software
- Supports 3D and virtual 7.1-channel surround sound
- LEDs indicate status, activity and speaker/microphone mute
- Plug and play—no external power supply required
- Compatible with Windows, Mac and Linux

System Requirements

- Available USB-A port
- 3.5 mm stereo speakers, headphones and/or microphone
- Windows 2000 and later, Mac OS X or Linux
- Windows XP, 7 and 8 (Xear 3D software)

Package Includes

- U237-001 USB External Sound Card
- Xear 3D software CD
- Quick Start Guide

AUDIO	
Audio Specification	7.1 Channel Surround Sound
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	0.5
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) 3.5MM (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Speaker/Mic Mute), Green (Active)
PHYSICAL	
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / in.)	5.80 x 2.17 x 4.20
Shipping Dimensions (hwd / cm)	14.73 x 5.51 x 10.67
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Clamshell
Unit Weight (lbs.)	0.02
Unit Weight (kg)	0.01
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)



Powering Business Worldwide



Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.