

Dual-Port USB Wall Charger with PD Charging - USB-C (39W) & USB-A (5V 2.4A/12W)

MODEL NUMBER: U280-W02-A1C1



Dual USB wall charger quickly charges a USB-C device and a USB-A device, including tablets and smartphones, at the same time.

Features

Dual USB Wall Charger Charges 2 Mobile Devices Simultaneously This dual-port USB wall charger with Quick Charge 2.0 technology lets you quickly and safely charge one USB-C mobile device and USB-A mobile device at the same time. Plug into any NEMA 1-15R, NEMA 5-15R or NEMA 5-15/20R outlet to ensure your smartphones, tablets and MP3 players, to name just a few devices, receive a satisfactory battery charge. The dual USB wall charger is compatible with Apple, Android, Windows and Amazon devices with USB-C, Thunderbolt 3 or USB-A charging ports.

USB-C PD Charging Port Supports Quick Charge 2.0 Technology The USB-C port is PD 2.0 compatible, supporting Quick Charge 2.0 Class A 5/9/12V technology. Instead of charging at a preset power level, this dual-port USB wall charger adapter adjusts to provide as much power as your QC-compliant device's battery can handle. Available outputs include 5V/3A (15W), 9V/3A (27W) and 15V/2.6A (39W), which can charge your QC 2.0 device much faster than traditional chargers.

Built-In Auto-Sensing Adjusts to Proper Power Level The USB-A port features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers.

Folding Plug Design Perfectly Sized for Travel The dual USB travel charger is easy to carry in your purse, suitcase, backpack or laptop bag. The NEMA 1-15P plug folds into the unit when not in use to shield it from damage and prevent it from snagging or scratching your bag's contents.

Specifications

OVERVIEW	
UPC Code	037332214416
Product Type	Wall Charger
Charging Form Factor	Direct Plug-In

Highlights

- Ideal for charging smartphones, tablets, e-readers and MP3 players while traveling
- USB-C PD Charging port supports Quick Charge 2.0 Class A 5/9/12V technology
- Auto-sensing USB-A port adjusts charging power level to your device up to 5V 2.4A
- Maximum charging power output of 51W: 39W USB-C and 12W USB-A
- Plug folds inward to protect it from damage and help the unit fit into a purse or bag

Applications

- Charge up to 2 smartphones, tablets, cameras, e-readers or any other USB-C, Thunderbolt 3 or USB-A devices

Package Includes

- U280-W02-A1C1 Dual-Port USB Wall Charger with PD Charging



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Device Compatibility	Phone; Tablet; Amazon Kindle; Laptop; Chromebook
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Input Connection Type	NEMA 1-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
Input Current	1.5A
OUTPUT	
Overload Protection	Yes
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	USB A (FEMALE); USB C (FEMALE)
CHARGING	
Number of Charging Ports	2
Total Charging Amps	1.5A
Total Charging Watts	51
Charging Method	USB
Charging Method Detail	Power Deliver 2.0; Quick Charge 2.0
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	USB-C: 39WUSB-A: 5V 2.5A (12W)
Charging Ports / Amps	(1) 2.4A; (1) 3A / 2.6A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	1.46 x 5.51 x 5.35
Shipping Dimensions (hwd / cm)	3.71 x 14.00 x 13.59
Shipping Weight (lbs.)	0.41
Shipping Weight (kg)	0.19
Unit Dimensions (hwd / in.)	2.900 x 2.500 x 1.200
Unit Dimensions (hwd / cm)	7.5 x 6.3 x 3
Unit Packaging Type	Box



Powering Business Worldwide



Unit Weight (lbs.)	0.30
Unit Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	32° to 95°F (0° to 35°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Operating Humidity Range	30 TO 90% RH, Non-Condensing
Storage Humidity Range	10 TO 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed
Product Compliance	RoHS; REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.