

Dual-Port USB Wall Charger with PD Charging - USB-C (39W) & USB-A (5V 2.4A/12W)

MODEL NUMBER: U280-W02-A1C1



Dual USB wall charger quickly charges a USB-C device and a USB-A device, including tablets and smartphones, at the same time.

Features

Dual USB Wall Charger Charges 2 Mobile Devices Simultaneously This dual-port USB wall charger with Quick Charge 2.0 technology lets you quickly and safely charge one USB-C mobile device and USB-A mobile device at the same time. Plug into any NEMA 1-15R, NEMA 5-15R or NEMA 5-15/20R outlet to ensure your smartphones, tablets and MP3 players, to name just a few devices, receive a satisfactory battery charge. The dual USB wall charger is compatible with Apple, Android, Windows and Amazon devices with USB-C, Thunderbolt 3 or USB-A charging ports.

USB-C PD Charging Port Supports Quick Charge 2.0 Technology The USB-C port is PD 2.0 compatible, supporting Quick Charge 2.0 Class A 5/9/12V technology. Instead of charging at a preset power level, this dual-port USB wall charger adapter adjusts to provide as much power as your QC-compliant device's battery can handle. Available outputs include 5V/3A (15W), 9V/3A (27W) and 15V/2.6A (39W), which can charge your QC 2.0 device much faster than traditional chargers.

Built-In Auto-Sensing Adjusts to Proper Power Level The USB-A port features auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers.

Folding Plug Design Perfectly Sized for Travel The dual USB travel charger is easy to carry in your purse, suitcase, backpack or laptop bag. The NEMA 1-15P plug folds into the unit when not in use to shield it from damage and prevent it from snagging or scratching your bag's contents.

Specifications

| OVERVIEW | |
|----------------------|----------------|
| UPC Code | 037332214416 |
| Product Type | Wall Charger |
| Charging Form Factor | Direct Plug-In |

Highlights

- Ideal for charging smartphones, tablets, e-readers and MP3 players while traveling
- USB-C PD Charging port supports Quick Charge 2.0 Class A 5/9/12V technology
- Auto-sensing USB-A port adjusts charging power level to your device up to 5V 2.4A
- Maximum charging power output of 51W: 39W USB-C and 12W USB-A
- Plug folds inward to protect it from damage and help the unit fit into a purse or bag

Applications

- Charge up to 2 smartphones, tablets, cameras, e-readers or any other USB-C, Thunderbolt 3 or USB-A devices

Package Includes

- U280-W02-A1C1 Dual-Port USB Wall Charger with PD Charging



| | |
|------------------------------------|--|
| Device Compatibility | Phone; Tablet; Amazon Kindle; Laptop; Chromebook |
| Over Current Protection | Yes |
| Technology | USB |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC; 230V AC |
| Input Connection Type | NEMA 1-15P |
| Voltage Compatibility (VAC) | 100; 110; 120; 125; 127; 200; 208; 220; 230; 240 |
| Input Frequency | 50/60Hz |
| Input Plug Type | NEMA 1-15P (NON-POLARIZED) |
| Input Current | 1.5A |
| OUTPUT | |
| Output Capacity | 51W |
| Overload Protection | Yes |
| CHARGING | |
| Number of Charging Ports | 2 |
| Total Charging Amps | 1.5A |
| Total Charging Watts | 51 |
| Charging Method | USB |
| Charging Port Type | USB A (FEMALE); USB C (FEMALE) |
| Charging Ports Details | USB-C: 39W USB-A: 5V 2.5A (12W) |
| Charging Ports / Amps | (1) 2.4A; (1) 3A / 2.6A |
| Charging Method Detail | Power Deliver 2.0; Quick Charge 2.0 |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Plastic |
| Shipping Dimensions (hwd / cm) | 3.71 x 14.00 x 13.59 |
| Shipping Dimensions (hwd / in.) | 1.46 x 5.51 x 5.35 |
| Shipping Weight (kg) | 0.19 |
| Shipping Weight (lbs.) | 0.41 |
| Unit Dimensions (hwd / cm) | 7.5 x 6.3 x 3 |
| Unit Dimensions (hwd / in.) | 2.9 x 2.5 x 1.2 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.14 |



| | |
|--------------------------------------|--------------------------------|
| Unit Weight (lbs.) | 0.30 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 95 F (0 to 35 C) |
| Storage Temperature Range | -4 to 185 F (-20 to 85 C) |
| Operating Humidity Range | 30 TO 90% RH, Non-Condensing |
| Storage Humidity Range | 10 TO 90% RH, Non-Condensing |
| CONNECTIONS | |
| Ports | 2 |
| Side A - Connector 1 | NEMA 1-15P (NON-POLARIZED) |
| Side B - Connector 1 | USB A (FEMALE); USB C (FEMALE) |
| FEATURES & SPECIFICATIONS | |
| Driver Required | No |
| Quick Charge Compliant | No |
| Overcurrent Protection | Yes |
| Overvoltage Protection | Yes |
| GaN Technology | No |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to FCC, RoHS, REACH, UL |
| Approvals | UL Listed - E471186 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>