

## USB 3.1 Gen 2 (10 Gbps) 2.5 in. SATA SSD/HDD to USB-C Enclosure Adapter with UASP Support, Thunderbolt 3 Compatible

MODEL NUMBER: U457-025-CG2



Durable lightweight enclosure connects a 2.5 in. SATA SSD or HDD to your computer's USB-C or Thunderbolt™ 3 port and performs fast file transfers at USB 3.1 Gen 2 speeds. UASP-enabled for 70% more speed with UASP host controller.

### Description

The U457-025-CG2 USB 3.1 Gen 2 (10 Gbps) SATA SSD/HDD to USB-C Enclosure Adapter lets you connect a high-performance SATA solid state drive (SSD) or hard disk drive (HDD) to a computer or laptop with a USB-C or Thunderbolt 3 port. Not only does it support USB 3.1 Gen 2 data transfer rates up to 10 Gbps, but it reads data up to 70 percent faster and writes up to 40 percent faster when connected to a UASP-enabled host controller.

Recommended for storing and sharing large files, such as photos, music and video files, the U457-025-CG2 accepts 2.5-inch SATA drives up to 2 TB. You can access data on an older SATA drive, or use a new SATA drive for additional storage space. The adapter is plug-and-play, so no software, drivers or external power supply is required, and it is backward compatible with previous USB generations. A blue LED indicates data is being read, written or transferred. Slim aluminum case stores conveniently in a backpack or laptop bag for use anywhere.

### Features

#### Connects an Internal SATA Drive to Your Computer's USB-C or Thunderbolt 3Port

- Recommended for storing and sharing large photo, music and video files
- Supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps
- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller
- Compatible with all USB-enabled operating systems

#### Compatible with 2.5 in. SATA Drives Up to 2 TB

- Accepts SATA III, II and I SSDs and HDDs
- Will support higher-capacity drives when available
- Backward compatible with previous USB generations
- Blue LED indicates drive data is being read, written or transferred

#### Designed for Immediate Use

- Plug and play—no software, drivers or external power supply needed

### Highlights

- Compatible with 2.5 in. SATA SSDs and HDDs up to 2 TB
- Supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps
- Works up to 70% faster when connected to UASP host controller
- Durable slim design perfectly sized for backpack or laptop bag
- Plug-and-play—no software, drivers or external power supply

### System Requirements

- Computer with USB-C or Thunderbolt 3 port (USB 3.1 Gen 2 port required for maximum speed)
- 2.5 in. SATA SSD or HDD (9.5 mm max height)

### Package Includes

- U457-025-CG2 USB 3.1 Gen 2 SATA SSD/HDD to USB-C Enclosure Adapter
- USB 3.1 Gen 2 Micro-B to USB-C cable, 2 ft.
- Mini screwdriver
- (2) Screws
- Storage sleeve
- Owner's manual

- Durable slim aluminum case perfectly sized for backpack or laptop bag
- Enclosed housing protects drive in applications requiring more durability
- USB 3.1 Gen 2 Type-C cable included

## Specifications

OVERVIEW	
UPC Code	037332202420
Drives Supported	2.5" HDD and SSD
Technology	SATA/eSATA
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	5
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Power)
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Shipping Dimensions (hwd / in.)	1.89 x 7.13 x 5.04
Shipping Dimensions (hwd / cm)	4.80 x 18.11 x 12.80
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	0.512 x 5.079 x 2.953
Unit Dimensions (hwd / cm)	1.3 x 12.9 x 7.5
Unit Packaging Type	Box
Unit Weight (lbs.)	0.14



Powering Business Worldwide



Unit Weight (kg)	0.06
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	50° to 122°F (10° to 50°C)
Storage Temperature Range	32° to 149°F (0° to 65°C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	17.1 BTU/Hr
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	Yes
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.