

USB-A Port Blockers with Reusable Key, 4 Pack, TAA

MODEL NUMBER: U2BLOCK-A-KEY



Block empty USB ports to prevent accidental or unauthorized connection of devices that could upload malware or copy private data.

Features

Secure USB Port Blockers Protect Your Data Against Unauthorized Access

These port blockers are an easy way to prevent unapproved personnel from connecting an unwanted flash drive or other USB peripheral to a USB-A port. Use the included security key to insert a blocker into the USB port and lock it into place. This will prevent any USB peripheral from infecting the device with malware or removing classified data. The key also removes the blocker just as easily and quickly as it installs the blocker. Four blockers are included, three of which conveniently store inside a compartment on the key. The key and blockers can only be used together for maximum security.

Highlights

- Port blockers help prevent unwanted thumb drives and other devices from connecting
- Can only be locked and unlocked with included security key to ensure protection
- Includes 4 blockers—3 store conveniently inside the key for safekeeping
- Blockers and key must be used together for security purposes
- Portable pocket-sized key and blockers are compatible with all USB-A ports

Applications

- Protect a USB device from damage or unauthorized access by blocking the port and preventing a peripheral from connecting

Package Includes

- (4) Port blockers
- Reusable key
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332253590
Accessory Type	Port Blocker
Accessory Class	USB Accessories
INPUT	
Product Length (in.)	2.822
Product Length (cm.)	7.71
Product Length (ft.)	0.235
Product Length (m)	0.0717
CONNECTIONS	
Side A - Connector 1	USB A (MALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	USB A (MALE)
Contact Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	Plastic
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	-40° to 185°F (-40° to 85°C)
Storage Temperature Range	-58° to 221°F (-50° to 105°C)
Operating Humidity Range	0 - 95 % RH, Non-Condensing
Storage Humidity Range	0 - 95 % RH, Non-Condensing
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC/EN 62040
Product Compliance	RoHS; CE (Europe); REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.