



USB 3.2 Gen 1 SuperSpeed Device Cable (A to B M/M) Black, 10 ft. (3.05 m)

MODEL NUMBER: U322-010-BK





Highlights

- 10-ft SuperSpeed USB 3.2 Gen 1 A-B Cable
- 10 times faster than USB 2.0 with transfer rates up to 5 Gbps

System Requirements

• Computers and peripherals with USB 3.2 Gen 1 capability

Package Includes

 10-ft. USB 3.2 Gen 1 SuperSpeed A-B Device Cable -Black

Connect USB 3.2 Gen 1 computers to USB 3.2 Gen 1 enabled peripherals such as hard drives and printers.

Features

- 10-ft USB 3.2 Gen 1 SuperSpeed Cable Black
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps
- Sync-N-Go technology minimizes user wait-time
- Provides Optimized Power Efficiency...No device polling and lower active and idle power requirements
- Backwards compatible with USB 2.0. Devices operate with USB 2.0 platforms. Hosts support USB 2.0 legacy devices

Specifications

OVERVIEW		
UPC Code	037332183132	
Technology	USB 3.x	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	USB B (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
Connector Style	Straight	





PHYSICAL		
Material of Construction	PVC	
Cable Jacket Color	Black	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.5MM	
Cable Length (ft.)	10	
Cable Length (m)	3.05	
Cable Length (in.)	120	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.28	
Shipping Weight (kg)	0.13	
ENVIRONMENTAL		
Operating Temperature Range	14° to 140°F (-10° to 60°C)	
Storage Temperature Range	-4° to 185°F (-20° to 85°C)	
Relative Humidity	10% to 85%, Non-Condensing	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.