

1-Port USB 3.0 SuperSpeed Desktop Extension Cable (M/F), 6 ft. (1.83 m)

MODEL NUMBER: U324-006-DSK1



Extends your desktop computer's existing USB 3.0 port up to 6 ft. away. Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices.

Features

Extends an Existing USB 3.0 Port an Extra 6 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices

Enjoy SuperSpeed Transfer Rates in High-End Applications

- Supports data transfer rates up to 5 Gbps—10x the speed of USB 2.0
- Bi-directional interface allows data to flow both directions at the same time, increasing theoretical bandwidth by 10x
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding blocks EMI/RFI interference
- Molded nickel-plated connectors ensure excellent connectivity
- Integral strain relief for cable and connectors' long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

Specifications

Highlights

- Supports data transfer rates up to 5 Gbps
- Bi-directional interface allows data to flow both directions
- Backward compatible with previous USB generations
- Double-shielded protection against EMI/RFI line noise
- Black padded non-sliding base

System Requirements

- Computer, laptop or other device with USB 3.0 port (to achieve USB 3.0 speeds)

Package Includes

- U324-006-DSK1 1-Port USB 3.0 SuperSpeed Desktop Extension Cable (M/F), 6 ft.



OVERVIEW	
UPC Code	037332199461
Over Current Protection	Yes
Technology	USB; USB 3.0 (SuperSpeed)
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5mm
Color	Black
Material of Construction	PVC
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>