



USB to Gigabit Ethernet NIC Network Adapter with 3 Port USB 3.x (5Gbps) Hub

MODEL NUMBER: U336-U03-GB











Add a Gigabit Ethernet port and 3-port USB 3.0 hub to your computer through one USB 3.0 SuperSpeed port.

Description

The U336-U03-GB USB 3.0 SuperSpeed to Gigabit Ethernet NIC Network Adapter allows you to turn a single SuperSpeed USB 3.0 computer port into an RJ45 Gigabit network port. It also creates three new additional USB 3.0 hub ports with each port supporting data transfer speeds up to 5 Gbps. This USB 3.0-based NIC lets you connect to your home or office network at full Gigabit speeds with support for 10/100/1000 Mbps. It supports features such as Wake-on-LAN (WoL), VLAN tagging and Jumbo Frames.

The U336-U03-GB is backward compatible with USB 2.0 and USB 1.x standards and will support older USB devices. It can also be used with older systems that do not have USB 3.0 ports (network speed limited by USB 1.x/2.0 bus), allowing you to utilize USB 3.0/2.0/1.x devices.

Features

- Combines a USB 3.0 SuperSpeed 3-Port hub with a Gigabit Ethernet adapter
- Supports data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and 1.1 devices (at USB 2.0 and 1.1 speeds)
- Gigabit Ethernet port supports true 10/100/1000 Mbps network speeds
- IEEE 802.3az (Energy Efficient Ethernet) compliant
- Supports IPv4 and IPv6 pack Checksum Offload Engine (COE) to reduce CPU loading
- Both full-duplex and half-duplex operations are supported
- Supports Wake-on-LAN, Jumbo Frames and VLAN tagging
- RealTek RTL8153 chipset

Specifications

OVERVIEW	
UPC Code	037332182579

Highlights

- Combines a USB 3.0 SuperSpeed 3-Port hub with a Gigabit Ethernet adapter
- Backward compatible with USB 2.0 and 1.1 devices (at USB 2.0 and 1.1 speeds)
- Gigabit Ethernet port supports true 10/100/1000 Mbps network speeds

System Requirements

- Available USB port
- Windows® XP, Vista®, 7, 8, 8.1 and 10
- Mac® OS X 10.6 through 10.12
- Linux® Kernel 2.6.14 and later

Package Includes

- U336-U03-GB
- Quick Start Guide





Product Type	Hub
Technology	Cat5/5e; Cat6; USB 3.x
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Built-In Cable Length (ft.)	0.98
Built-In Cable Length (m)	0.30
Built-In Cable Length (in.)	11.81
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / in.)	1.12 x 2.90 x 5.70
Shipping Dimensions (hwd / cm)	2.84 x 7.37 x 14.48
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.14 x 3.04 x 9.6
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)





FEATURES & SPECIFICATIONS		
USB Hub Ports	Yes	
Number of USB Hub Ports	3	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)	
STANDARDS & COMPLIANCE		
TAA Compliant Option	N	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.