

3-Port USB-C Hub with LAN Port and Power Delivery, USB-C to 3x USB-A Ports and Gbe, USB 3.0, White

MODEL NUMBER: U460-003-3AG-C



Adds USB-C PD charging, Gigabit Ethernet and 3 USB-A ports to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook or tablet.

Features

Portable USB 3.1 Hub Turns Your Device's USB-C or Thunderbolt 3 Port into a Workstation This USB-C adapter with Power Delivery (PD) Charging expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

PD Charging Port Charges the Connected Chromebook, MacBook Pro or Other Device The USB-C PD charging port provides power and charging to the connected PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone). Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W). That's sufficient wattage to fast-charge, sync and power most high-capacity devices, including the MacBook Pro. Note: USB-C PD port does not support Quick Charge (QC)

Connects USB Peripherals and Transfers Data at Fast USB 3.1 Gen 1 Speeds Three USB-A ports transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0, between your device and up to three USB peripherals, such as a flash drive, printer and keyboard/mouse. The USB Battery Charging (BC) 1.2 port provides power output up to 5V 1.5A (5W) for charging a connected device. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. Note: Host must support USB OTG (On-the-Go)

Accesses a Wired Gigabit Ethernet Network The RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (Tripp Lite N201-Series Cat6 cables sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play

Highlights

- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Power Delivery cable provides 3A (60W) power output for charging connected device
- Connects you to a wired 10/100/1000 Ethernet network when Wi-Fi is unavailable
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Save data from your computer to a USB thumb drive or external hard drive
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a USB microphone/headset to record a podcast or listen to music
- Write a report using a USB keyboard with your tablet or Android phone

System Requirements

- Source device with USB-C or Thunderbolt 3 port
- Ethernet network with speeds up to 1000 Mbps

Package Includes

- U460-003-3AG-C USB 3.1 Gen 1 Portable Hub/Adapter
- Owner's manual

USB-C dock is specifically designed for use with the MacBook Pro, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or drivers. It's smaller than a standard smartphone, making it easy to pack into a pocket, backpack or laptop bag for multiport convenience wherever you go.

Specifications

OVERVIEW	
UPC Code	037332193810
Product Type	Hub
Technology	Cat5/5e; Cat6
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Video Ports	(3) USB A (FEMALE)
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	2.50

USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	20V/3A
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green - Power, Orange - Activity
CHARGING	
Total Charging Watts	60
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	(1) 1.5A; (1) 3A
PHYSICAL	
Color	White
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	5.51 x 0.91 x 3.94
Shipping Weight (lbs.)	0.13
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	8.5 BTU/Hr
Operating Humidity Range	10 - 85 % RH, Non-Condensing
Storage Humidity Range	5 - 90 % RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output USB port
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
CONNECTIONS	
Number of Ports	5

Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty