

USB 3.2 Gen 1 to SATA/IDE Adapter with Built-In USB Cable, 2.5 in., 3.5 in. and 5.25 in. Hard Drives

MODEL NUMBER: **U338-06N**



Connects a SATA or IDE (PATA) hard drive to your laptop or computer's USB port for extra storage, quick disk formatting and fast data transfer.

Features

Quickly Connects a SATA and/or IDE Drive to Your Computer's USB Port

This USB-A to SATA/IDE Adapter connects a 2.5-, 3.5- or 5.25-inch SATA or IDE hard drive to an available USB-A port on your laptop or computer. This lets you back up important data, retrieve data from an old hard drive or store information on an external drive that you can take with you to another computer. Blue LEDs indicate successful connection and data transfer.

Compatible with SATA and IDE Drives Up to 4 TB

The U338-06N accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives for sharing large files, such as music and video, at speeds up to 5 Gbps. It features 40- and 44-pin IDE ports, as well as 7-pin SATA data and 15-pin SATA power (via adapter cable) connectors. Necessary SATA and Molex cables are included.

Easy to Use

The plug-and-play adapter requires no additional software to download. SATA and Molex cables and an external power supply are included. The U338-06N is compatible with all USB-enabled operating systems.

Specifications

OVERVIEW	
UPC Code	037332199744
Technology	SATA/eSATA
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America

Highlights

- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Compatible with SATA and IDE hard drives up to 4 TB
- Backward compatible with earlier USB generations
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with all USB-enabled operating systems

System Requirements

- Any USB-enabled operating system
- Available USB-A port (USB 3.2 Gen 1 required to achieve USB 3.2 Gen 1 speeds)
- 2.5 in., 3.5 in. or 5.25 in. SATA or IDE drive

Package Includes

- U338-06N USB to SATA/IDE Adapter
- 7-pin SATA data cable
- 15-pin SATA power cable
- 4-pin Molex power cable
- External power supply (Input: 100-240V, 50/60 Hz, 0.6A; Output: 12V 2A) with NEMA 1-15P plug and 5 ft. (1.5 m) cord
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
AC Power Adapter Output Specs (V / A)	12V / 2A
AC Power Adapter Cord Length (ft.)	4.9
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	21.6
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A
DC Barrel Plug	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	24.00
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	7 PIN SATA (MALE)
Side B - Connector 2	40 POS. SOCKET (FEMALE)
Side B - Connector 3	44 Header IDC (Female)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Power)
PHYSICAL	
Color	Black
Material of Construction	ABS
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	1.90 x 5.20 x 6.70
Shipping Dimensions (hwd / cm)	4.83 x 13.21 x 17.02
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	0.551 x 2.480 x 1.654
Unit Dimensions (hwd / cm)	1.4 x 6.3 x 4.2
Unit Packaging Type	Box



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (lbs.)	0.08
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	50° to 122°F (10° to 50°C)
Storage Temperature Range	32° to 149°F (0° to 65°C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	81.9 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; UL; cUL; RoHS
Product Certifications	UL Listed
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.