

Tripp Lite Waber Industrial Power Strip, 9-Outlet, 15 ft. (4.57 m) Cord - Accommodates 1 Transformer

MODEL NUMBER: **UL17CB-15**



Highlights

- 9 outlets
- 15-ft. (4.57 m) cord
- 12.5" length
- All metal housing
- 9th outlet on end panel

Package Includes

- UL17CB-15 Power Strip
- Warranty information
- Instruction manual

Description

This Waber-by-Tripp Lite UL17CB-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 9 NEMA 5-15R output receptacles, 1-8 with 1.125 inch center-to-center spacing and a 9th outlet placed away from the rest on the panel opposite the input line cord to accommodate large plugs with minimal blockage. Includes 15-ft. (4.57 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL17CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15 amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 9 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 9 NEMA 5-15R output receptacles, 1-8 with 1.125 inch center-to-center spacing and a 9th outlet placed away from the rest on the panel opposite the input line cord to accommodate large plugs with minimal blockage
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW



UPC Code	037332103512
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(9) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of 8 outlets, plus a 9th outlet placed away from the rest on the panel opposite the input line cord to accommodate transformers without blocking outlets
Right-Angle Outlets	No
Outlet Spacing	1-8 spaced 1.625 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Material of Construction	Metal
Color	Gray
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	27.4mm
Receptacle Color	Black



Shipping Dimensions (hwd / cm)	35.56 x 6.10 x 15.24
Shipping Dimensions (hwd / in.)	14.00 x 2.40 x 6.00
Shipping Weight (kg)	1.38
Shipping Weight (lbs.)	3.05
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>