

USB 3.0 SuperSpeed to DVI and HDMI Dual Monitor Video Display Adapter

MODEL NUMBER: U344-001-HDDVI



Description

The U344-001-HDDVI USB 3.2 Display Adapter enables the simultaneous connection of DVI and HDMI displays to a computer via a USB 3.2 port (a VGA monitor can be connected to the DVI-I port with an appropriate DVI to VGA adapter). Once the driver has been installed, the attached monitor(s) will be enabled immediately. The U344-001-HDDVI supports video resolutions up to 2048 x 1152 and video streaming up to 1080p. Up to three adapters can be connected to a single computer, allowing for up to six displays (see manual for minimum computer requirements). It supports USB 3.2 data transfer rates up to 5 Gbps, and is also backward compatible to USB 2.0. It is bus-powered from a computer's USB connection...no external power supply is required.

Features

- Add an HDMI and DVI monitor to your computer or laptop through a single USB 3.0 port
- DVI-I port allows for the connection of a VGA monitor using a DVI to VGA adapter
- Supports video resolutions up to 2048x1152
- Supports video streaming up to 1080p
- Up to 3 adapters can be connected to a single computer, allowing for the addition of up to 6 displays
- Display video in either mirror or extended modes
- Bus-powered, no external power supply required
- USB 3.0 supports data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0
- Automatically resumes from hibernation and suspend modes

Highlights

- Add an HDMI and DVI monitor to your computer or laptop through a single USB 3.0 port
- Supports video resolutions up to 2048x1152
- Up to 3 adapters can be connected to a single computer, allowing for the addition of up to 6 displays

System Requirements

- Compatible with Windows 7, Windows 10 and later. Supports both 32- and 64-bit.
- Compatible with Intel Mac OS X 10.8.5 / 10.11 and later. Supports both 32- and 64-bit.
- USB 2.0 or 3.0 port; USB 3.0 port required for USB 3.0 speeds
- VGA, DisplayPort, DVI or HDMI monitor
- See manual for minimum requirements for 1-2, 3, 4-6 monitors
- Compatible with Ubuntu 14.04.2

Package Includes

- U344-001-HDDVI
- Driver CD
- USB 3.0 Cable
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332186294
Technology	DVI; HDMI

VIDEO	
Max Supported Video Resolution	2048 x 1152 @ 60Hz
Max Supported Color Depth	24-bit True Color
3D Video Supported	No
INPUT	
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5V / 2.5A
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	Yes
POWER	
DC Barrel Plug	OD: 3.5 x 1.35 x 9.5mm, Positive Pin, Negative Sleeve
Output Volt/Amp (from external power supply)	5V/2.5A
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	DVI-I (FEMALE)
Side B - Connector 2	HDMI (FEMALE)
Side B - Connector 3	3.5mm x 1.35mm (5V DC Barrel)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power, DVI, HDMI)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	2.20 x 5.50 x 8.80
Shipping Dimensions (hwd / cm)	5.59 x 13.97 x 22.35
Shipping Weight (lbs.)	0.46
Shipping Weight (kg)	0.21
Unit Dimensions (hwd / in.)	0.940 x 5.000 x 2.370
Unit Packaging Type	Box
Unit Weight (lbs.)	0.46



Powering Business Worldwide



Unit Weight (kg)	0.21
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Relative Humidity	0% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Full Duplex Support	Yes
HDCP Specification	1.3
Driver Required	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.