

MODEL:

PDU3EVN6L2120

3-Phase Monitored Rack-Mount PDU



**208V
3-Phase
Input**



**NEMA
L21-20P
Plug**



**208V
Single-Phase
Output**



C19



5-15/20R




C13



**5.7kW
Load
Capacity**



**Touchscreen
LCD**



**Network
Interface**




**0U
Rack-Mount**




**Toolless
Mounting
Buttons**



- A** Color Touchscreen LCD
- B** C13, C19 and 5-15/20R Outlets with Multi-Function Bank LEDs
- C** C13 and C19 Plug Inserts
- D** Removable Mounting Brackets
- E** Toolless Mounting Buttons with Removable 90° Rotation Brackets
- F** 6 ft. Input Power Cord
- G** NEMA L21-20P Input Plug
- H** Durable Metal Case
- I** LX Platform Interface
- J** USB-B Port (for Direct Console Access)
- K** USB-A Ports (for EnviroSense2 Sensors)
- L** RJ45 Configuration Port
- M** Ethernet Port
- N** Network Interface Reset Button







AC Input Connection: Insert NEMA L21-20P plug into compatible utility, generator or UPS outlet.



Color Touchscreen LCD: Easily toggle between menus to monitor input current level per phase, output current per load bank, environmental sensor data and network information. It also generates a unique QR code to allow access to the monitored PDU through a mobile device.



LX Platform Interface: Connect to 10/100/1000 Mbps Ethernet networks for remote monitoring via SNMP, Web, SSH, or telnet.
*Add optional EnviroSense2 (E2) modules for temperature, humidity, and dry contact signaling.



Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

- Distributes power to 45 outlets (12 C13, 2 C19 & 1 5-15/20R per bank)
- Java-free, HTML5-based network interface allows for remote monitoring via SNMP, Web, SSH or telnet
- Displays load for each bank, phase and total output in real time with 1% billing-grade accuracy
- Perfect for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS









1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Specifications

| | |
|-------------------------|--|
| Model | PDU3EVN6L2120 |
| Voltage | 208V (3-Phase Input/Single-Phase Output) |
| Frequency | 50/60 Hz |
| Load Capacity | 5.7kW (208V/120V) |
| Input Plug | NEMA L21-20P |
| Input Cord Length | 6 ft. / 1.8 m |
| Outlets | 45 (36 C13 / 6 C19 / 3 5-15/20R) |
| Primary Mounting Option | 0U (Vertical) Rack-Mount |
| Unit Dimensions | 70 x 2.17 x 2.52 in. / 1778 x 55 x 64 mm |
| Unit Weight | 13.5 lb. / 6.1 kg |
| Standards | Tested to UL/CSA 60950-1 (US & Canada), NOM (Mexico), FCC Class A, RoHS, TAA Compliant |





Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.

MODEL:
PDU3EVN6L2120



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234

www.tripplite.com