



Device Drivers

A driver CD-ROM is no longer included with this product. The latest drivers for Windows, macOS, Android, Chrome OS and Ubuntu are available from the DisplayLink website. Please visit https://www.displaylink.com/downloads.

USB-C Dock, Dual Display - Dual HDMI, USB 3.x (5Gbps) Hub, GbE, 3.5 mm, 85W PD Charging

MODEL NUMBER: U442-DOCK20-B











USB-C dock with DisplayLink technology connects 2 HDMI monitors to your host device and extends/mirrors video to them simultaneously.

Features

USB-C Docking Station Turns Your Device's USB or Thunderbolt 3 Port into a WorkstationThis multiport USB-C dock with PD Charging expands the potential of your Windows laptop, Chromebook, tablet or other device with a USB-A, USB-C or Thunderbolt 3 port. It's ideal for transmitting 1080p video and digital audio to multiple large displays, adding a thumb drive and other USB peripherals, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

Transmits Crystal-Clear Hi-Def Video and Digital Audio to Multiple HDMI Displays Two HDMI outputs support individual high-definition resolutions up to 2560 x 1440 at 50 Hz. By downloading and installing the proper DisplayLink drivers to your host device, you may connect two HDMI displays simultaneously. This allows you to display the image from the host computer on both monitors, extend your host desktop across both with different windows open on each, or combine all into one large display as a video wall. Maximum resolution when both video ports are connected at the same time is 1920 x 1080 (1080p) at 60 Hz.

USB Hub Ports Connect Keyboards, Thumb Drives and Other PeripheralsThree USB-A hub ports accept USB peripherals, such as flash drives, mice, keyboards and printers. All support fast USB 3.2 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with USB 2.0 and USB 1.1 devices. One also supports BC 1.2 charging with 5V 1.5A (7.5W) of power dedicated to fast-charging your mobile device (and 2.4A for Apple devices). Note: Host must support USB OTG (On-the-Go).

PD Charging Port Charges the Connected Notebook, Tablet or Other DeviceConnect your host device to the USB-C Power Delivery port, which supports PD 3.0 charging of connected PD Charging-compliant devices, such as laptops, Kindles, iPads and Android smartphones, up to 20V 4.25A (85W). The included power supply, when plugged into an AC outlet, provides the charging power.

Accesses a Wired Gigabit Ethernet NetworkThe RJ45 port offers access to a Gigabit Ethernet network

Highlights

- Connects 2 external displays for easy multitasking and increasing productivity
- Supports 20V 4.25A (85W) power output for fast-charging large-capacity mobile devices
- Joins a wired 10/100/1000
 Gigabit Ethernet network when no Wi-Fi is available
- USB 3.2 Gen 1 Type-A data ports allow connection of flash drives and other peripherals
- Included USB-C to A adapter can connect to host device's USB-A port, if desired

Applications

- Extend or mirror your laptop or PC monitor on multiple displays to aid in multitasking and increase productivity
- Transfer data to and from a USB flash drive or external hard drive
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop through the USB-C PD Charging port
- Connect a microphone/headset to record a podcast or listen to music

System Requirements

- Source device with USB-A, USB-C or Thunderbolt 3 port and DisplayLink drivers installed
- Display device with HDMI input
- Any major operating system

Package Includes

- U442-DOCK20-B USB-C Dock, Dual Display, Black
- USB-C cable, 1 m
- USB-C to USB-A adapter
- External power supply (Input: 100–240V, 50/60 Hz, 2A; Output: 20V 5A)
- C5 to NEMA 5-15P Adapter, 6
- Owner's manual





when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Connects Speakers, Microphone and Other Audio EquipmentThe 3.5 mm mini stereo jack is convenient for connecting speakers, headphones or a microphone to your workstation. You can listen to music or record the latest episode of your podcast.

Anti-Theft Lock Protects the USB Docking Station When You Aren't AroundConnect a user-supplied computer/laptop security cable lock (not included) to this K-lock port to protect your source device against theft.

Detachable USB-C Cable Connects in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time. An included adapter allows you to connect the cable to your device's USB-A port, though the device will only charge when connected to the USB-C PD Charging port.

Specifications

OVERVIEW	
UPC Code	037332253460
Product Type	Docking Station
Technology	Cat5/5e; Cat6; HDMI; USB 3.x; Stereo Audio
Host Connector	USB A (MALE); USB C (MALE)
VIDEO	
Video Input	USB C (FEMALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	2
Video Ports	(2) HDMI (FEMALE)
Video Ports Details	HDMI 1.4
Resolutions Supported	HDMI Dual:1920 x 1200 60HzHDMI Single: 2560 x 1440 50Hz
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 1920x1200
Max Supported Video Resolution	Single: 2560 x 1440 @50Hz; Dual: 1080p @60Hz
Extended Mode	Yes
Extended Mode Details	2x HDMI (1080p). This is in addition to a built in monitor in the laptop or source device.
Mirror Mode	Yes
Mirror Mode Details	2x HDMI (1920 x 1200 60Hz incl. 1080p). This is in addition to a built in monitor in the laptop or source device.
HDR Support	No
3D Video Supported	No
AUDIO	
Audio Ports	3.5MM (FEMALE)





Audio Ports Details	3.5mm Combo Stereo Audio / Microphone Jack		
	·		
Audio Specification	2.1 Channel Surround Sound, TRRS		
DATA			
Data Ports	(3) USB A (FEMALE)		
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)		
NETWORK			
Network Ports	RJ45 (FEMALE)		
THOMAS OF STATE OF ST			
INPUT			
AC Power Adapter Plug(s)	NEMA 5-15P North America		
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 2A		
AC Power Adapter Output Specs (V / A)	20V / 5A		
AC Power Adapter Cord Length (ft.)	5.9		
AC Power Adapter Cord Length (m)	1.8		
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240		
Bus Powered	No		
BATTERY			
Battery Charging (5V/1.5A Port)	Yes		
POWER			
Power Source Type	AC Adapter with detachable power cord		
AC Adapter	Input: 100–240V, 50/60 Hz, 2A; Output: 20V, 5A		
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve		
Power Consumption (Watts)	15.00		
USB Power Delivery (PD) Charging Support	Yes		
USB Power Delivery (PD) Charging Specification	3.0		
CONNECTIONS			
Number of Ports	8		
Dock Connectors	(2) USB-A 3.2 Gen1, USB-A 3.2 Gen1 BC 1.2, USB-C PD Charging, (2) HDMI, RJ45, 3.5mm		
Side A - Connector 1	USB C (FEMALE)		
Side B - Connector 1	(2) HDMI (FEMALE)		
Side B - Connector 2	RJ45 (FEMALE)		





Side B - Connector 4	3.5MM (FEMALE)	
USER INTERFACE, ALERTS & CON		
LED Indicators	Green/Blue (Power/Active)	
CHARGING		
Total Charging Watts	100	
Charging Ports	USB-A: 5V 1.5A (7.5W) ; USB-C: 85W Power Delivery (PD 3.0)	
Charging Ports / Amps	1.5A; 5A	
PHYSICAL		
Color	Black	
Material of Construction	Plastic	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.0mm	
Cable Length (ft.)	3.28	
Cable Length (m)	1.00	
Unit Dimensions (hwd / in.)	3.740 x 3.740 x 1.330	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.4	
Unit Weight (kg)	0.18	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-4° to 158°F (-20° to 70°C)	
Relative Humidity	20% to 80% RH, Non-Condensing	
Operating Humidity Range	20% to 80% RH, Non-Condensing	
Storage Humidity Range	20% to 80% RH, Non-Condensing	
Power Provided to Connected Device(s)	USB-C PD: 20V/4.25A (85W), USB3.0-A: 5V/0.9A (4.5W), USB BC 1.2: 5V/1.5A (7.5W)	
COMMUNICATIONS		
Network Compatibility	1 Gbps (Gigabit)	
FEATURES & SPECIFICATIONS		
USB Hub Ports	Yes	
Number of USB Hub Ports	3	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)	
Ethernet Support	Yes	





UASP Support	No		
Auto MDIX Support	Yes		
Full Duplex Support	Yes		
Suspend Mode Support	Yes		
Remote Wakeup Support	Yes		
Driver Required	Yes		
Recommended Category Cable	Cat6 Cables		
STANDARDS & COMPLIANCE			
TAA Compliant Option	N		
External Power Supply Certifications	CE; GS; TUV; UL; cUL		
Product Compliance	RoHS; REACH; FCC (USA)		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	3-year limited warranty		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.