
SRCOOL24K

SmartRack® Self-Contained Portable Server-Rack Cooling Unit



Specifications	
Model	SRCOOL24K
Cooling Capacity	24,000 BTU / 7.0 kW
Input Voltage / Frequency	208/240V / 60 Hz
Power Consumption	2560W Max
Input Cord/ Connector	2 m (6.6 ft.) / NEMA L6-20P
Unit Dimensions (H x W x D)	970 x 521 x 551 mm / 38.2 x 20.5 x 21.7 in.
Shipping Dimensions (H x W x D)	1181 x 640 x 742 mm / 46.5 x 25.2 x 29.2 in.
Unit Weight	79.6 kg / 175.4 lb.
Shipping Weight	100.2 kg / 221 lb.
Standards	Meets UL 484, CSA, RoHS and NOM standards;
	R410A refrigerant

 Features remote control, web management and true spot-cooling capabilities with pre-installed SRCOOLNET2 accessory

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

