





Powering Business Worldwide

TRIPP LITE  
SERIES

(sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

**Allows External Memory Access**The memory card slots support Micro SD and SD/MMC cards for transferring data to and from your connected computer, laptop or tablet. Both slots may be used at the same time.

**Built-In USB-C Cable Attaches in Either Direction**Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

**Ready to Use Right from the Package, So You Can Plug and Play Immediately**The plug-and-play USB-C dock is specifically designed for use with Windows laptops and other notebooks, smartphones, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no extra software to be downloaded or installed. It's about the size of a smartphone, making it easy to pack into a pocket, backpack or laptop bag for multiport convenience wherever you go.

## Specifications

OVERVIEW	
UPC Code	037332241016
Product Type	Docking Station
Device Compatibility	Chromebook; Computer; Laptop; Monitor/HDTV; Phone
Technology	Cat5/5e; Cat6; HDMI; USB 3.x
Country/Region	Global
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE)
Video Ports Details	HDMI 1.4; HDCP 1.4
Resolutions Supported	3840 x 2160 (4K x 2K) @ 30 Hz
Supported Resolutions	3840x2160 (4K)
Max Supported Video Resolution	3840 X 2160 (4K X 2K) @ 30HZ
Recommended Cabling	<a href="#">P568-Series High Speed 4K HDMI Cables</a>
Extended Mode	Yes
Extended Mode Details	Extend your workspace to across a connected display at video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
Mirror Mode	Yes
Mirror Mode Details	Mirror video from the USB-C port on a laptop to a connected display at video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
Max Supported Color Depth	24-bit True Color
HDR Support	Yes

3D Video Supported	Yes
Chroma Sub Sampling	4:2:2; 4:4:4
EDID Support	Yes
Signal Transmission	Unidirectional
DisplayPort Alt Mode	Yes
DSC Support	Yes
<b>DATA</b>	
Data Ports	(3) USB A (FEMALE); (1) USB C (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps); (1) USB-C - USB 3.2 Gen 1 (5 Gbps)
<b>NETWORK</b>	
Network Ports	RJ45 (FEMALE)
<b>STORAGE</b>	
Card Slots	SD (FEMALE); MICRO SD (FEMALE)
Card Slots Details	SD 3.0 Memory Card slots (SD and MicroSD) can be used simultaneously
<b>INPUT</b>	
Bus Powered	Yes
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	Yes
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
<b>CONNECTIONS</b>	
Number of Ports	8
Ports	1
Ports Detail	Connect to a wired Gigabit Ethernet network via the built-in RJ45 port on the dock.
Dock Connectors	USB-C PD Data/Charging, (3) USB-A 3.2 Gen 1, MICRO SD, SD, HDMI, RJ45
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	(3) USB A (FEMALE)
Side B - Connector 4	USB C (FEMALE)

Side B - Connector 5	MICRO SD (FEMALE)
Side B - Connector 6	SD (FEMALE)
Connector Plating	Nickel
Connector Style	Straight
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	White (Connection to Power) and Orange (Activity)
<b>CHARGING</b>	
Number of Charging Ports	4
Total Charging Amps	2
Total Charging Watts	100
Charging Port Type	(3) USB A (FEMALE); USB C (FEMALE)
Charging Ports	USB-C: 100W (20V 5A) Power Delivery (PD 3.0); USB-A: 5V 1.5A (7.5W)
Charging Ports Details	One USB-A port supports 5V 1.5A (7.5W) for quickly charging mobile devicesAll three USB-A ports share 5V 2A (10W) when connected to a PD 3.0 compliant chargerThe USB-C PD Charging/Data port provides up to 20V 5A (100W) to charge the host laptop via a compatible wall charger
Charging Ports / Amps	1.5A; 5A
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Aluminum
Connector Color	Gray
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.2mm
Cable Length (ft.)	0.39
Cable Length (m)	0.12
Cable Length (in.)	4.72
Cable Length (cm)	12
Total Number of Ports	8
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	0.500 x 4.100 x 1.900
Unit Dimensions (hwd / cm)	1.3 x 10.5 x 4.9
Unit Packaging Type	Box



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Weight (lbs.)	0.25
Unit Weight (kg)	0.11
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-A: 5V/2A (10W), USB-C PD: 20V/5W (100W)
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit)
EDID Compatible	Yes
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	5 Gbps
MST Support	No
Multi-Resolution Support	No
Network Speed Support	10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit)
Ethernet Support	Yes
UASP Support	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
SD Card Specification	SD; Micro SD
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
Product Certifications	ICES (Canada); NOM (Mexico)



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.