


EVMAGU23A-E G4 MANAGED

FUNCTIONALITY CURRENT, POWER, AND ENERGY METERING FOR INPUT; CURRENT METERING FOR BRANCH	INPUT EATON/SOURIAU UTG SERIES 8-PIN CONNECTOR CORDSETS NOT INCLUDED, MUST BE ORDERED SEPARATELY	OUTPUT (12) IEC 60320 C13 (12) EATON C39 - COMBO C13/C19	ENVIRONMENTAL 0° TO 60° C 32° TO 140° F
MECHANICAL 55.91" (1420mm) LENGTH 2.05" (52mm) WIDTH 2.56" (65mm) DEPTH ALUMINUM CHASSIS, BLACK	INPUT RATING 1P: 100-240V~, 16-63A, or 3P DELTA: 100-240V~, 16-55A, or 3P WYE: 100-240 / 173-415V~, 16-32A 50/60Hz; USE WITH E21 SERIES CORDSET (CBL3XX-XX)	OUTPUT RATING 100-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT CORDSET RATING	CERTIFICATIONS cTUVus CE, UKCA, RCM
CIRCUIT BREAKERS (6) 20A 2-POLE LISTED	COMMUNICATION G4 eNMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY	ACCESSORIES INCLUDED SPK045 - INSTALLATION OPTIONAL USB-C TO RS232 ADAPTER - U209-006-RJ45XC OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2	REGULATORY MODEL EMAF-ZBAK-G3BK



METRIC	THIRD ANGLE PROJECTION	NAME (PART NUMBER): 9001-22392-EVMAGU23A-E	REVISION:	EATON
DESCRIPTION:	PDU G4 MA OU UNV23KW-END 12xC13 12xC39	SCALE: 0.400	STATE:	SHEET: 1 OF 1
ORIGINATED BY:	SEE NOTES FOR TOLERANCES DIM ARE IN MM (INCHES) AFTER PLATING INTERPRET DIM AND TOL PER ASME Y14.5-2018	ECC:		