

USB-C to HDMI Active Adapter Cable (M/M), 4K, Black, 6 ft. (1.8 m)

MODEL NUMBER: U444-006-H



Connects your existing HDMI TV, monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, smartphone or PC.

Features

Connects an HDMI Display to Your USB-C or Thunderbolt 3 Device Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode Ideal for giving video presentations, editing multiple documents or streaming 4K video for digital signage Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps

Common Applications Extends 4K video from your primary display to another Duplicates the same video on 2 displays Converts a secondary display to your primary display

Crystal-Clear 4K Video and Digital Audio Supports UHD video resolutions up to 3840 x 2160 (4K) @ 30 Hz Supports 36-bit Deep Color (12 bits per channel) Supports per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR)

Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Premium Construction Gold-plated connectors and contacts for maximum conductivity and minimum data loss Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data Integral strain relief helps cable and connectors move freely without stress or cracking Durable PVC jacket designed to last a long time

Ready for Instant Use Plug-and-play operation with no software, drivers or external power required 6 ft. length easy to manage in crowded environments Backward compatible with non-4K displays

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD video resolutions up to 4K @ 30 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input

Package Includes

- U444-006-H USB 3.1 Gen 1 USB-C to HDMI 4K Adapter Cable (M/M), 6 ft.

Specifications

| OVERVIEW | |
|--------------|--------------|
| UPC Code | 037332202468 |
| Product Type | Active Cable |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|---------------------------------|-------------------------|
| Technology | HDMI |
| VIDEO | |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 30Hz |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 72 |
| Product Length (cm.) | 182.88 |
| Product Length (ft.) | 6 |
| Product Length (m) | 1.83 |
| BATTERY | |
| Battery Charging (5V/1.5A Port) | No |
| POWER | |
| Power Consumption (Watts) | 0.60 |
| CONNECTIONS | |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | HDMI (MALE) |
| Connector Plating | Gold |
| PHYSICAL | |
| Color | Black |
| Material of Construction | PVC, ABS |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Cable Length (in.) | 72 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.30 |
| Shipping Weight (kg) | 0.14 |
| Unit Dimensions (hwd / in.) | 9.000 x 7.000 x 0.500 |
| Unit Packaging Type | Polybag |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|--|
| Unit Weight (lbs.) | 0.22 |
| Unit Weight (kg) | 0.10 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 113°F (0° to 45°C) |
| Storage Temperature Range | 14° to 158°F (-10° to 70°C) |
| BTUs | 2.1 BTU/Hr |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| IP68 Rated | No |
| IP20 Rated | No |
| UASP Support | No |
| Auto MDIX Support | No |
| Full Duplex Support | No |
| Suspend Mode Support | No |
| Remote Wakeup Support | No |
| HDCP Specification | 1.4 |
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | ICES (Canada) |
| Product Compliance | CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.