

USB-C to HDMI Adapter Cable (M/M), 4K, 4:4:4, Thunderbolt 3 Compatible, White, 6 ft.

MODEL NUMBER: U444-006-HWE



USB-C to HDMI cable directly connects an HDMI monitor to your MacBook Pro, Windows laptop or tablet's USB-C or Thunderbolt 3 port.

Features

USB-C to HDMI Converter Connects a USB-C or Thunderbolt 3 Port to a 4K Monitor This USB Type-C to HDMI adapter (M/M) connects an HDMI monitor, projector or television to the USB-C or Thunderbolt 3 port on your MacBook Pro or Windows laptop. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger 4K screen. No other adapter or cable is needed to complete your 4K connection. The U444-006-HWE is uni-directional and only converts from USB-C to HDMI.

Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video Signals By connecting the USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to an HDMI monitor, television or projector without installing special software drivers.

Enjoy the Clarity of True 4K HDMI Video with Multi-Channel Audio and 4:4:4 Color This 4K HDMI cable supports true 4K resolutions up to 4096 x 2160 (4K x 2K) at 30 Hz, as well as HDCP 1.4 and HDMI 1.4 specifications. It also supports 36-bit Deep Color and 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB Type-C to HDMI cable requires no software or external power. Just connect the USB-C plug to the USB-C or Thunderbolt 3 port on a source device that supports USB DisplayPort Alternate Mode, and connect the HDMI plug to your display. The six-foot USB 3.1 Gen 1 cable is backward compatible with previous USB and HDMI generations, so you can use it with legacy equipment.

Highlights

- Converts audio/video signals from sources supporting USB DisplayPort Alt Mode
- Supports resolutions up to true 4K @ 30 Hz (4:4:4) for crystal-clear video with audio
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation
- Uni-directional 6 ft. cable directs A/V signals only from USB-C to HDMI

Applications

- Watch 4K video content from a MacBook Pro or Windows laptop on an Ultra HD television, monitor or projector
- Connect a tablet, smartphone or other USB-C source to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Link an HDTV to your PC for use as a 4K monitor

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input

Package Includes



- U444-006-HWE USB-C to HDMI Adapter Cable, M/M, White, 6 ft.

Specifications

OVERVIEW	
UPC Code	037332253927
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Bus Powered	Yes
PHYSICAL	
Cable Jacket Type	TPE
Cable Outer Diameter (OD)	4.2MM
Color	White
Material of Construction	TPE, ABS
Wire Gauge (AWG)	34/24
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	HDMI: 3840 X 2160, Including 4096 x 2160 (4K X 2K) @ 30HZ
HDMI Specification	1.4



HDCP Specification	1.4
Driver Required	No
Max Supported Color Depth	36-bit Deep Color
Technology	HDMI; USB; USB 3.1 (Gen 1)
Chroma Sub Sampling	4:2:2; 4:4:4
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>