

USB-C to Mini Displayport Adapter Cable, 4K 60Hz, Black, 6 ft.

MODEL NUMBER: **U444-006-MDP**



Connects your existing Mini DisplayPort (mDP) monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, smartphone or PC. Saves you the clutter and expense of additional cables, adapters and displays.

Description

The U444-006-MDP USB 3.1 Gen 1 USB-C to Mini DisplayPort 4K Adapter Cable (M/M) helps you transmit digital audio and 4K video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to an mDP-enabled monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video for digital signage in crystal-clear 4K.

With a source device that also supports USB DisplayPort Alternate Mode, you can extend 4K video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary. By connecting to an existing mDP display, you'll save the clutter of adding more cables and adapters.

The plug-and-play U444-006-MDP requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. Then, connect the mDP plug to your display.

This six-foot cable supports UHD video resolutions up to 3840 x 2160 (4K) at 60 Hz, 36-bit Deep Color (12 bits per channel) and per-lane transfer rates of 5.4 Gbps (HBR2), 2.7 Gbps (HBR) and 1.62 Gbps (RBR). It also supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps. Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data.

Note: This cable is uni-directional. Will only work from a USB-C port to Mini DisplayPort

Features

Connects a Mini DisplayPort Display to Your USB-C or Thunderbolt 3 Device Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode ideal for giving video presentations, editing multiple documents, or streaming 4K video for digital signage Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Supports DisplayPort 1.2 specifications Extend 4K video from your primary display to another, duplicate the same video on both, or convert a secondary display to be the primary display

Crystal-Clear 4K Video and Digital Audio Supports UHD video resolutions up to 3840 x 2160 (4K) @ 60 Hz Supports 36-bit Deep Color (12 bits per channel) Supports per-lane transfer rates of 5.4 Gbps (HBR2),

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD video resolutions up to 4K @ 60 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with Mini DisplayPort input

Package Includes

- U444-006-MDP USB 3.1 Gen 1 USB-C to Mini DisplayPort 4K Adapter Cable (M/M), 6 ft.



2.7 Gbps (HBR) and 1.62 Gbps (RBR)

Reversible USB-C ConnectorFumble-free reversible USB-C plug connects in either direction for quick connection every time

Premium ConstructionGold-plated connectors and contacts for maximum conductivity and minimum data lossFoil and braid shielding protects against EMI/RFI line noise that can distort or destroy dataIntegral strain relief helps cable and connectors move freely without stress or crackingDurable PVC jacket designed to last a long time

Ready for Instant UsePlug-and-play operation with no software, drivers or external power required6 ft. length easy to manage in crowded environmentsBackward compatible with non-4K displays

Specifications

OVERVIEW	
UPC Code	037332193841
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.828
Bus Powered	Yes
Product Length (in.)	72
Product Length (cm.)	182.88
Product Length (ft.)	6
Product Length (m.)	1.83
BATTERY	
Battery Charging (5V/1.5A Port)	No
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	PVC, ABS
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.19
Unit Packaging Type	Polybag
Unit Weight (kg)	0.08
Unit Weight (lbs.)	0.18
ENVIRONMENTAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.1 BTU/Hr
Power Consumption (Watts)	0.6
Operating Humidity Range	10% to 85% RH, non-condensing
Storage Humidity Range	5% to 90% RH, non-condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MINI DISPLAYPORT (MALE)
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	MDP: 3840 X 2160 (4K) @ 60HZ
Displayport Specification	1.2
HDCP Specification	1.3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Technology	USB 3.1 (Gen 1); USB; DisplayPort
SPECIAL FEATURES	
HDR Support	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>