

USB-C to DVI Adapter with PD Charging, Black

MODEL NUMBER: U444-06N-DB-C



USB-C adapter adds DVI and USB-C PD ports to your laptop, MacBook, Chromebook or other compatible device.

Features

USB to DVI Adapter Connects to Your Device's USB-C or Thunderbolt 3 Port This USB-C adapter helps you transmit video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a DVI-enabled television, monitor or projector. It's ideal for transmitting 1080p video to a large display, as well as powering and charging a PD Charging-compliant mobile device. **Supports USB DisplayPort Alternate Mode for Transmitting Video Signals**

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 1080p Video to a DVI Display To send high-definition video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The DVI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

Charges the Connected Laptop, Smartphone or Other Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the adapter is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W. Note: USB-C PD port does not support Quick Charge (QC).

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB to DVI adapter requires no software, drivers or external power. It's smaller than a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty The U444-06N-DB-C is backed by a 3-year warranty, ensuring reliability and performance.

Specifications

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- USB-C PD charging port supports power input up to 20V 3A (60W)
- Easy installation with plug-and-play operation—no software required

Applications

- Play 1080p video from your laptop or PC on a DVI display
- Give a video presentation at a meeting, training session or conference
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor
- Edit large documents on two different monitors

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input (DVI port)

Package Includes

- U444-06N-DB-C USB-C to DVI Adapter w/PD Charging - USB 3.1, Thunderbolt 3, 1080p, Black
- Owner's manual

OVERVIEW	
UPC Code	037332210715
Technology	DVI
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	DVI-I DUAL LINK (FEMALE)
Number of Monitors Supported	1
Video Ports	DVI-I DUAL LINK (FEMALE)
Resolutions Supported	1920 x 1080 (1080p) @ 60Hz
Supported Resolutions	1920x1080 (1080p)
Max Supported Video Resolution	DVI: 1920 x 1080 (1080p) @ 60Hz
Extended Mode	Yes
Mirror Mode	Yes
HDR Support	No
3D Video Supported	No
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	11.0
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Consumption (Watts)	0.6
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0

CHARGING	
Number of Charging Ports	1
Total Charging Watts	60
Charging Method	AC
Charging Port Type	USB C (FEMALE)
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	Charge the host PC with up to 20V/3A (60W) of power
Charging Ports / Amps	3A / 2A / 1.5A
Charging Amps per Port	3
PHYSICAL	
Color	Black
Material of Construction	PVC, ABS
Cable Jacket Rating	VW-1
Number of Displays	1
Shipping Dimensions (hwd / in.)	0.79 x 4.60 x 3.90
Shipping Dimensions (hwd / cm)	2.01 x 11.68 x 9.91
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / in.)	0.550 x 2.300 x 1.600
Unit Packaging Type	Box
Unit Weight (lbs.)	0.07
Unit Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	2.1 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C)
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB C (MALE)

Side B - Connector 1	DVI-I DUAL LINK (FEMALE)
Side B - Connector 2	USB C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Hub Ports	No
Number of USB Hub Ports	0
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Multi-Resolution Support	No
HDCP Specification	1.2
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty