

## USB-C Multiport Adapter - HDMI, USB 3.0 Port, GbE, 60W PD Charging, HDCP, Black

MODEL NUMBER: U444-06N-HGUB-C



Adds HDMI, USB-A, USB-C PD charging and Gigabit Ethernet ports to your tablet, laptop, notebook, smartphone or PC.

### Features

#### Mini Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport Workstation

This USB-C to HDMI cable expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting digital audio and 1080p video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

#### Supports USB DisplayPort Alternate Mode for Transmitting Audio/Video DisplayPort and USB Signals

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

#### Transmits Crystal-Clear 1080p Video and Digital Audio to an HDMI Display

To send digital audio and HD video to an HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (sold separately). The HDMI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

#### Connects a USB Peripheral

The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with USB 2.0 and USB 1.1 devices. The port provides up to 5V/1.5A (7.5W) of fast-charging power to mobile devices. **Note:** Host must support USB OTG (On-the-Go).

#### Charges a Connected Device

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the U444-06N-HGUB-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W). **Note:** USB-C PD port does not support Quick Charge (QC).

#### Accesses a Wired Gigabit Ethernet Network

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

#### Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

#### Ready to Use Right Out of the Package

### Highlights

- Transmits DisplayPort signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @60 Hz
- USB-A port provides up to 5V 1.5A (7.5W) of fast-charging power
- Connects you to a wired Ethernet network when no Wi-Fi is available
- USB-C PD 3.0 port supports 20V 3A (60W) power output for charging host device

### Applications

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Transfer data from a USB flash drive or connect your computer to a USB printer or other USB device
- Charge your connected notebook or laptop by connecting its wall charger to the USB-C PD Charging port

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input (HDMI port)

### Package Includes

- U444-06N-HGUB-C USB-C Multiport Adapter, Black
- Owner's manual



The plug-and-play USB 3.1 to HDMI adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

## Specifications

OVERVIEW	
UPC Code	037332209160
Product Type	Multiport Adapter
Technology	Cat5/5e; Cat6; HDMI
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE)
Video Ports Details	HDMI 1.3; HDCP 1.3
Resolutions Supported	HDMI: 1080P 60Hz (1920 x 1080)
Max Supported Video Resolution	HDMI: 1920 X 1080 (1080P) @ 60HZ
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	USB A (FEMALE)
Data Ports Details	USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0



<b>CHARGING</b>	
Total Charging Watts	60
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	1.5A; 3A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PVC, ABS
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.50
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.57 x 1.57 x 3.15
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	9 BTU/Hr
Power Consumption (Watts)	2.60
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
IEEE Standards Supported	802.3; 802.3u; 802.3az; 802.3x
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	USB 3.0 A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Side B - Connector 4	RJ45 (FEMALE)
Connector Plating	Nickel



<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
UASP Support	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>