

USB-C Multiport Adapter, 4K HDMI, VGA, White

MODEL NUMBER: **U444-06N-HV4K**



Connects your existing 4K HDMI or 1080p VGA TV, monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U444-06N-HV4K USB 3.1 Gen 1 USB-C to HDMI/VGA 4K Adapter (M/2xF) helps you transmit digital audio and video from your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC to a high-definition television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen or streaming video for digital signage.

With a source device that also supports USB DisplayPort Alternate Mode, you can extend video from your primary display to another, duplicate the same video on both displays or change the second display to your primary.

The plug-and-play USB-C to HDMI adapter requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. Then, connect the HDMI port or the HD15 port to your HDMI or VGA display using a compatible cable (sold separately).

The U444-06N-HV4K meets HDCP 1.4 specifications. It supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz and VGA video resolutions up to 1920 x 1200 (including 1080p) at 60 Hz. It also supports 36-bit Deep Color (12 bits per channel) and 300 MHz/3 Gbps per channel bandwidth (9 Gbps total). The HDMI port delivers rich 7.1-channel surround sound.

Features

Connects an HDMI or VGA Display to Your USB-C or Thunderbolt 3 Device

- Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode
- Ideal for giving video presentations, editing multiple documents or streaming video for digital signage

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports VGA video resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI or VGA input

Package Includes

- U444-06N-HV4K USB 3.1 Gen 1 USB-C to HDMI/VGA 4K Adapter (M/2xF)
- Owner's manual



- Supports 300 MHz/3 Gbps per channel bandwidth (9 Gbps total)
- Meets HDCP 1.4 specifications

Common Applications

- Extends video from your primary display to another
- Duplicates the same video on 2 displays
- Converts a secondary display to your primary display

Crystal-Clear Video and Digital Audio

- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports VGA video resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Supports 36-bit Deep Color (12 bits per channel)
- Supports 7.1-channel surround sound (HDMI only)

Built-In Cable with Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Ready for Instant Use

- Plug-and-play operation with no software, drivers or external power required
- About the size of a credit card for easy carrying in a pocket, purse or laptop bag
- Backward compatible with non-4K displays

Specifications

| OVERVIEW | |
|--------------------------------|---|
| UPC Code | 037332205704 |
| Product Type | Multiport Adapter |
| Technology | HDMI; USB 3.1 (Gen 1); VGA/SVGA |
| Host Connector | USB C (MALE) |
| VIDEO | |
| Number of Monitors Supported | 1 |
| Video Ports | HDMI (FEMALE); HD15 (FEMALE) |
| Video Ports Detail | HDMI 1.4; HDCP 1.4 |
| Resolutions Supported | HDMI: 4K 30Hz (3840 x 2160) VGA: 1920 x 1200 60Hz |
| Max Supported Video Resolution | HDMI: 3840 X 2160 (4K X 2K) @ 30HZ; VGA: 1920 X 1200 (1080P) @ 60HZ |
| Extended Mode | No |
| Mirror Mode | No |



| AUDIO | |
|---------------------------------|--|
| Audio Specification | 7.1 channel surround sound via HDMI port |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 6 |
| Product Length (cm.) | 15.24 |
| Product Length (ft.) | 0.5 |
| Product Length (m.) | 0.15 |
| BATTERY | |
| Battery Charging (5V/1.5A Port) | No |
| PHYSICAL | |
| Cable Jacket Rating | VW-1 |
| Color | White |
| Material of Construction | PVC, ABS |
| Unit Dimensions (hwd / cm) | 1.4 x 4 x 6 |
| Unit Dimensions (hwd / in.) | 0.55 x 1.65 x 2.36 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.03 |
| Unit Weight (lbs.) | 0.07 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 113 F (0 to 45 C) |
| Storage Temperature Range | 14 to 158 F (-10 to 70 C) |
| BTUs | 2.2 BTU/Hr |
| Power Consumption (Watts) | 0.65 |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| CONNECTIONS | |
| Ports | 2 |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | HD15 (FEMALE) |
| Side B - Connector 2 | HDMI (FEMALE) |



| | |
|--------------------------------------|--|
| Connector Plating | Nickel |
| Contact Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| HDMI Specification | 1.4 |
| HDCP Specification | 1.4 |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>