

USB-C Multiport Adapter, VGA, USB 3.x (5Gbps) Hub Port, Gigabit Ethernet and 60W PD Charging, White

MODEL NUMBER: U444-06N-VGU-C



Mini docking station adds VGA, USB-A, USB-C PD charging and Gigabit Ethernet ports to the USB-C port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U444-06N-VGU-C USB 3.2 Gen 1 USB-C to VGA Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C port. It's ideal for transmitting 1080p video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time. With a source device that also supports USB DisplayPort Alternate Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

The plug-and-play U444-06N-VGU-C requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

To send HD video to a VGA television, projector or monitor, connect the VGA port to the display using a VGA cable (sold separately). The VGA port supports HD video resolutions up to 1920 x 1200 (1080p) at 60 Hz.

The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.2 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with previous USB generations. The port provides up to 5V/1.5A (7.5W) of fast-charging power to mobile devices.

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook or Chromebook) the U444-06N-VGU-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Features

Mini Docking Station Turns Your Device's USB-C Port into a Multiport Workstation Ideal for transmitting video to a large display, adding a USB peripheral, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network simultaneously Plug-and-play operation with no software, drivers or external power required About the size of a credit card for easy carrying in a pocket, purse or laptop bag

Transmit Crystal-Clear 1080p Video to VGA Display Compatible with USB-C source devices that support USB DisplayPort Alternate Mode Supports HD video resolutions up to 1920 x 1200 (1080p) @ 60 Hz Extends video from your primary display to another Duplicates the same video on 2 displays Converts a secondary display to your primary display

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting video
- Supports HD video resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Supports true 10/100/1000 Mbps Ethernet network speeds
- USB-C PD charging port supports power input up to 20V 3A (60W)
- USB-A port provides up to 5V/1.5A (7.5W) of fast-charging power
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C port that supports USB DisplayPort Alternate Mode
- Display device with VGA input (VGA port)

Package Includes

- U444-06N-VGU-C USB 3.2 Gen 1 USB-C to VGA Adapter, White
- Owner's manual



Powering Business Worldwide

TRIPP LITE SERIES

Connect a USB Peripheral USB-A port accepts flash drives, mice, keyboards, printers and other USB peripherals Supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps Backward compatible with USB 2.0 and USB 1.1 Fast charging USB port provides up to 1.5A of fast-charging power to mobile devices. Note: Host must support USB OTG (On-the-Go)

Charge a Connected Device USB-C PD port connects to wall charger to power and charge the connected PD Charging-compliant USB-C device Supports power input up to 20V 3A (60W) Note: USB-C PD port does not support Quick Charge (QC).

Access a Wired Gigabit Ethernet Network RJ45 port supports true 10/100/1000 Mbps network speeds Recommended for a faster wired network connection or getting online when no Wi-Fi is available

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

OVERVIEW	
UPC Code	037332193728
Product Type	Multiport Adapter
Technology	Cat5/5e; Cat6; VGA/SVGA; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	1
Video Ports	HD15 (FEMALE)
Resolutions Supported	VGA: 1920 x 1200 60Hz
Max Supported Video Resolution	VGA: 1920 X 1200 (1080P) @ 60HZ
Extended Mode	Yes
Mirror Mode	Yes
DATA	
Data Ports	USB A (FEMALE)
Data Ports Details	USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5



Powering Business Worldwide

TRIPP LITE
SERIES

Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	2.20
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	USB 3.0 A (FEMALE)
Side B - Connector 3	RJ45 (FEMALE)
Side B - Connector 4	USB C (FEMALE)
Connector Plating	Nickel
CHARGING	
Total Charging Watts	60
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	1.5A; 3A
PHYSICAL	
Color	White
Material of Construction	PVC, ABS
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	0.791 x 1.500 x 1.650
Unit Packaging Type	Box
Unit Weight (lbs.)	0.11
Unit Weight (kg)	0.05



Powering Business Worldwide

TRIPP LITE
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	7.6 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A), Up to 20V 3A (60W) Input (USB-C)
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3u; 802.3az; 802.3x
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.