

## 4-Port USB-C Hub - USB 3.x Gen 2 (10Gbps), 2x USB-A & 2x USB-C Ports, Thunderbolt 3, Aluminum Housing

MODEL NUMBER: U460-004-2A2C-2



USB 3.2 Gen 2 portable hub adds 2 USB-A and 2 USB-C ports to the USB-C or Thunderbolt 3 port on your MacBook Pro or Windows laptop.

### Features

**USB 3.2 Hub Connects 4 USB Peripherals to Your Windows or Mac Computer** This USB-C hub allows you to connect up to four USB peripherals to your MacBook Pro, Windows laptop or other tablet, smartphone or computer with a USB-C or Thunderbolt 3 port. You can expand the capability of your device by connecting USB peripherals that can help you do your job faster, easier and better, such as an external hard drive, keyboard/mouse, power meter and printer. **Note:** Host must support USB OTG (On-the-Go).

**Transfers Data at Lightning-Fast USB 3.2 Gen 2 Speeds** Two USB-C and two USB-A ports transfer data at speeds up to 10 Gbps, which is double the speed of USB 3.2 Gen 1, and share 900mA of power for charging devices. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

**Built-In USB-C Cable Connects in Either Direction** Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. A blue LED indicates whether the hub is connected properly.

**Ready to Use Right Out of the Package** The bus-powered USB-C hub is specifically designed for use with the MacBook Pro, Windows laptops, Chromebooks and other notebooks, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no drivers or external power. The lightweight aluminum case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

## Specifications

OVERVIEW	
UPC Code	037332251718
Product Type	Hub
Technology	USB 3.x

### Highlights

- Bus-powered USB hub is compatible with all USB-C and Thunderbolt 3 devices
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Supports USB 3.2 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no drivers required for easy, immediate installation

### Applications

- Connect up to 4 USB peripherals, such as an external hard drive, MP3 player, power meter and printer
- Transfer files quickly to and from a USB thumb drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone
- Download photos from a digital camera

### System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.2 Gen 2 capability required for 10 Gbps speeds)

### Package Includes

- U460-004-2A2C-2 4-Port USB-C Hub



Powering Business Worldwide



Host Connector	USB C (MALE)
<b>VIDEO</b>	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(2) USB A (FEMALE); (2) USB C (FEMALE)
Data Ports Details	(2) USB-A - USB 3.2 Gen 2 (10 Gbps); (2) USB-C - USB 3.2 Gen 2 (10 Gbps)
<b>INPUT</b>	
Built-In Cable Length (ft.)	0.492
Built-In Cable Length (m)	0.15
Built-In Cable Length (in.)	5.905
Built-In Cable Length (cm)	15
Product Length (in.)	8.523
Product Length (cm.)	21.66
Product Length (ft.)	0.711
Product Length (m)	0.216
<b>CONNECTIONS</b>	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Side B - Connector 4	USB C (FEMALE)
Connector Plating	Nickel
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Transmitting Data (Blue)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	0.492



Powering Business Worldwide



Cable Length (m)	0.15
Cable Length (in.)	5.905
Cable Length (cm)	15
Unit Dimensions (hwd / in.)	2.366 x 0.374 x 1.563
Unit Packaging Type	Box
Unit Weight (lbs.)	0.0926
Unit Weight (kg)	0.04
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 140°F (0° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0 ~ 90 % NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.