

Keyspan USB to Serial Adapter - USB-A Male to DB9 RS232 Male, 3 ft. (0.91 m), TAA

MODEL NUMBER: USA-19HS



Connects devices with a 9-pin serial port, such as switches, routers, barcode scanners and lab equipment, to your computer or laptop's USB-A port.

Features

Works with RS-232 Serial Devices Connects to switches, routers, barcode scanners, GPS units, point-of-sale devices, lab equipment, network storage devices, modems, graphics tablets and other devices with a DB9 serial port. Supports data transfer speeds up to 230 Kbps—twice as fast as a built-in serial port.

Easy to Set Up and Use Right Out of the Box

No external power supply is needed and only one connection is required. Simply connect the included three-foot (0.9-meter) USB cable between the unit's USB-B port and your computer's USB-A port. The unit is compatible with any USB cable up to 16 feet (4.9 meters). A green LED indicates data activity at a glance. The unit weighs only 2 ounces for convenient transport in a backpack or laptop bag.

Compatible with Major Operating Systems Works with Microsoft Windows (up to Windows 11) and macOS X (up to Ventura 13.3.1), and includes Windows line monitor and data trace software. The unit supports both 32-bit and 64-bit systems and has continuously updated drivers available for download on the unit's Technical Support page.

TAA-Compliant for GSA Schedule Purchases The USA-19HS is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Supports data transfer speeds up to 230 Kbps to ensure reliable data transfers
- Detachable 3 ft. USB cable included
- Plug-and-play operation with no software required for easy, immediate installation
- Works with 32- and 64-bit Windows and macOS X (see [model support page](#))

System Requirements

- Computer with an available USB-A port
- Compatible with Windows 2000, XP, Vista, 7, 8, 10, 11, Windows 2008 Server R2, Windows Server 2012
- Compatible up to macOS Ventura 13.3.1

Note: Computer should have Administrator access to avoid potential installation issues when first installing drivers. When attempting to use most recent driver with an existing USA-19HS unit, it is critical that the old drivers be uninstalled from the computer before downloading and installing the newer driver. Even though the old driver no longer works, the Device Manager will still attempt to use it.

Package Includes

- USA-19HS Keyspan High-Speed RS232 to USB Adapter
- USB-A cable, 3 ft. (0.91 m)
- Owner's Manual

Specifications

| OVERVIEW | |
|----------------------|--------------------------|
| UPC Code | 672603000413 |
| Device Compatibility | Printer; Router; Scanner |
| Technology | USB |
| Country/Region | Global |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|--------------------------|
| Host Connector | USB A (MALE) |
| INPUT | |
| Bus Powered | Yes |
| CONNECTIONS | |
| Side A - Connector 1 | USB A (MALE) |
| Side B - Connector 1 | DB9 (MALE) |
| Connector Plating | Nickel |
| Contact Plating | Gold |
| Connector Style | Straight |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Outer Diameter (OD) | 3.8mm |
| Wire Gauge (AWG) | 28 |
| Cable Length (ft.) | 1 |
| Cable Length (m) | 0.30 |
| Cable Length (in.) | 36 |
| Cable Length (cm) | 30.48 |
| Total Number of Ports | 2 |
| Shipping Dimensions (hwd / in.) | 3.00 x 9.00 x 6.00 |
| Shipping Dimensions (hwd / cm) | 7.62 x 22.86 x 15.24 |
| Shipping Weight (lbs.) | 0.40 |
| Shipping Weight (kg) | 0.18 |
| Unit Dimensions (hwd / in.) | 0.950 x 1.630 x 3.070 |
| Unit Dimensions (hwd / cm) | 2.42 x 4.13 x 7.81 |
| Unit Dimensions (hwd / mm) | 24.2 x 41.3 x 78.1 |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 2.0 (up to 480 Mbps) |
| Cable Compatibility | DB9 (Female) |
| Driver Required | Yes |
| STANDARDS & COMPLIANCE | |
| Product Certifications | EN 55024; EN 55032 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|--|
| Product Compliance | CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; Trade Agreements Act (TAA); UKCA; WEEE |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.