## CSC16AC / CSC16ACW

## 16-Device AC Charging Station



16 Ultrabooks



Load Rating



Construction



**Locking Doors** 




Adjustable Storage Shelf Dividers



**Ample Airflow** 

- A Locking Split Doors **B** AC Charger Unit
- Adjustable Storage Shelves (Holds up to 16 Devices)
- D Blanking Panel (Removable)
- Power Cord Access Holes (1 Located on Each Side)
- F Padlock Hasp (User Supplies Lock)
- G Cable Lock Routing Holes (User Supplies Lock)
- H Rear Panel with Keyhole Wall Mount Slots
- Keys



- · Locking steel cabinet wth charging, secure storage and cord management for up to 16 Ultrabooks, tablets and other devices
- Supports iPad®, Android™, Surface™ and Kindle tablets
- · Adjustable/removable storage shelf dividers accommodate thicker devices
- · Door locks with included keys prevent device theft, damage or tampering


## SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS





1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

	(VL) NOM 🔂
Specifications	NOI-I
Model	CSC16AC / CSC16ACW
Maximum Devices Per Shelf	16
AC Receptacles	16 x 5-15R
Equipment Mounting Depth	15.4 in. / 390.5 mm
Load Rating*	200 lbs. / 90 kg
Unit Dimensions (H x W x D)	18.8 x 30.3 x 21.6 in. / 475.4 x 770.4 x 547.5 mm
Unit Weight	97 lb. / 43.6 kg
Power Requirement	120V AC 50/60 Hz, 12A
Standards	Meets UL 60950, NOM (Mexico) and
	RoHS standards

\*The load rating includes the combined weight of the unit and installed equipment. The unit must be mounted to a stable surface with user-supplied anchors capable of bearing the full load.









1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.