

MODEL:

# PDU3EVN10L2130

## 3-Phase Monitored 0U Vertical PDU



208V  
3-Phase Input



NEMA L21-30P  
Plug



208/120V  
Single-Phase  
Output



45 Total Outlets



C13



5-15/20R



8.6kW Load  
Capacity



Touchscreen  
LCD



Network  
Interface





0U  
Rackmount







Toolless  
Mounting  
Buttons

- A** Color Touchscreen LCD
- B** C13, C19 and 5-15/20R Outlets with Multi-Function LEDs
- C** 20A 2-Pole Hydraulic Magnetic Circuit Breakers
- D** C13 and C19 Plug Inserts
- E** Removable Mounting Brackets
- F** Toolless Mounting Buttons with Removable 90° Rotation Brackets
- G** 10 ft. Input Power Cord
- H** NEMA L21-30P Input Plug
- I** LX Platform Interface
- J** USB-B Port (for Direct Console Access)
- K** USB-A Ports (for EnviroSense2 Sensors)
- L** RJ45 Configuration Port
- M** Ethernet Port
- N** Network Interface Reset Button

Color Touchscreen LCD: Easily toggle between menus to monitor input current level per phase, output current per load bank, environmental sensor data and network information. It also generates a unique QR code to allow access to the monitored PDU through a mobile device.



LX Platform Interface: Connect to 10/100/1000 Mbps Ethernet networks for remote monitoring via SNMP, Web, SSH, or Telnet. \*Add optional EnviroSense2 (E2) modules for temperature, humidity, and dry contact signaling.



Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

- Distributes power to 45 outlets (36 C13, 6 C19 & 3 5-15/20R)
- Java-free, HTML5-based network interface allows for remote monitoring via SNMP, Web, SSH or Telnet
- Displays load for any output phase in real time
- Perfect for rack-mount server, network and telecom applications






SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

### Specifications

Model	PDU3EVN10L2130
Voltage	200/120V (3-Phase Input, Single-Phase Output)
Frequency	50/60 Hz
Load Capacity	8.6kW
Input Connector	NEMA L21-30P Input Plug
Cord Length	10 ft. / 3 m
Outlets	45 (36 C13 / 6 C19 / 3 5-15/20R)
Primary Mounting Option	0U (Vertical) Rack-mount
Unit Dimensions	70 x 2.17 x 2.52 in. / 1778 x 55 x 64 mm
Unit Weight	13.5 lb. / 6 kg
Standards	Tested to UL 60950-1 (US & Canada), NOM (Mexico), FCC Class A; RoHS; TAA



1111 W. 35th Street  
Chicago, IL 60609 USA  
773.869.1234  
www.tripplite.com



Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

MODEL:  
**PDU3EVN10L2130**

**TRIPP-LITE**

1111 W. 35th Street  
Chicago, IL 60609 USA  
773.869.1234  
www.triplite.com