

MODEL:

PDU3EVS6H50

3-Phase Switched Rack-Mount PDU



208/240V
3-Phase Input



50A Hubbell
CS8365C Plug



208/240V
Single-Phase
Output



30 Outlets



14.5kW Load
Capacity



Touchscreen
LCD



Network
Interface




0U
Rack-Mount




Toolless
Mounting
Buttons


- A** Color Touchscreen LCD
- B** C13 and C19 Outlets with Multi-Function LEDs
- C** 20A 2-Pole Hydraulic Magnetic Circuit Breakers
- D** C13 and C19 Plug Inserts
- E** Removable Mounting Brackets
- F** Toolless Mounting Buttons with Removable 90° Rotation Brackets
- G** 6 ft. Input Power Cord
- H** 50A Hubbell CS8365C Input Plug
- I** Durable Metal Case
- J** LX Platform Interface
- K** USB-B Port (for Direct Console Access)
- L** USB-A Ports (for EnviroSense2 Sensors)
- M** RJ45 Configuration Port
- N** Ethernet Port
- O** Network Interface Reset Button







H AC Input Connection: Insert 50A Hubbell CS8365C plug into compatible utility, generator or UPS outlet.



A Color Touchscreen LCD: Easily toggle between menus to monitor input current level per phase, output current per load bank, environmental sensor data and network information. It also generates a unique QR code to allow access to the monitored PDU through a mobile device.



J LX Platform Interface: Connect to 10/100/1000 Mbps Ethernet networks for remote monitoring via SNMP, Web, SSH, or telnet.
*Add optional EnviroSense2 (E2) modules for temperature, humidity, and dry contact signaling.



F Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

- Distributes power to 30 outlets (8 C13 & 2 C19 per bank)
- Java-free, HTML5-based network interface allows for remote monitoring via SNMP, Web, SSH or telnet
- Displays load for each bank, phase and total output in real time with +/- 1% billing grade accuracy
- Perfect for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS









1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Specifications

Model	PDU3EVS6H50
Voltage	208/240V (3-Phase Input/Single-Phase Output)
Frequency	50 / 60 Hz
Load Capacity	12.6kW (208V), 13.3kW (220V), 13.9kW (230V), 14.5kW (240V)
Input Plug	50A Hubbell CS8365C
Input Cord Length	6 ft. / 1.8 m
Outlets	30 (24 C13 / 6 C19)
Primary Mounting Option	0U (Vertical) Rack-Mount
Unit Dimensions	70 x 2.17 x 2.49 in. / 1778 x 55 x 63 mm
Unit Weight	18.25 lb. / 8.28 kg
Standards	Tested to UL 60950-1 (US & Canada), NOM (Mexico), FCC Class A, TAA Compliant





MODEL:
PDU3EVS6H50



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234

www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.