PDU3XVSR6G32B

3-Phase Switched Rackmount PDU
























Toolless Mounting **Buttons**

- 380V 415V 3-Phase Input 309 (3P+N+E)
 - Plug
- Single-Phase Output
- 30 Outlets
- 23kW Load Capacity
- Multimode
 - **Load Meter**
- Network Interface
- Rackmount

- A Multimode Load Meter
- **B** C13 and C19 Outlets with Multi-Function LEDs
- **C** 20A Single Pole Hydraulic **Magnetic Circuit Breakers**
- D C13 and C19 Plug Inserts
- **E** Removable Mounting **Brackets**
- F Toolless Mounting **Buttons with Removable** 90° Rotation Brackets
- **G** 6 ft. Input Power Cord
- H 32A Red IEC-309 (3P+N+E) Input Plug (IP44)
- Durable Metal Case
- Network Interface
- **RJ45 Ethernet Jack**
- Manual Configuration Port
- Environmental **Monitoring Port**









Multimode Load Meter: Display the load for any phase, bank or outlet, display temperature or humidity*, display the IP address or rotate the display 180°.


Network Interface: Connect to Ethernet for remote monitoring and individual outlet control via SNMP, Web or Telnet.


*Add optional ENVIROSENSE accessory for temperature/humidity monitoring and

dry contact interface









Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

Specifications	ROHS
Model	PDU3XVSR6G32B
Voltage	380V - 415V (3-Phase Input/Single-Phase Output)
Frequency	50 / 60 Hz
Load Capacity	23kW
Input Plug	32A Red IEC-309 (3P+N+E)
	(IP44 Protection Rating - Splash-Proof)
Input Cord Length	6 ft.
Outlets	30 (24 C13 / 6 C19)
Primary Mounting Option	0U (Vertical) Rackmount
Unit Weight & Dimensions	15.9 lbs / 70 x 2.17 x 2.52 (HxWxD in inches)
	7.2 kg / 177.8 x 5.5 x 6.4 (HxWxD in cm)
	See next page for detailed unit measurements.
Standards	Tested to EN 60950-1, CE Class A,
	IP44 Protection Rating (Plug)
Tripp Lite has a policy of continuous im	provement. Specifications are subject to change without notice.

- Distributes power to 30 outlets (8 C13 & 2 C19 per phase)
- · Remote monitoring and control via SNMP, Web or Telnet
- · Displays load for each bank, phase, and outlet in real time
- · Perfect for rackmount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

