

MODEL:

PDUMNV20HV2LX

Monitored Rack-Mount PDU



High Voltage Input/Output



3.3/3.7kW Load Capacity



20 Outlets



C13



L6-20P Plug



20A Max Capacity



Load Meter



HTML5 Network Interface



0U Rackmount



Toolless Mounting Buttons




AC Inlet Supports International Plugs




TAA Compliant

- A** Digital Load Meter
- B** C13 and C19 Outlets
- C** C20 Inlet
- D** Plug-Lock Insert Sleeves
- E** Removable Mounting Bracket
- F** Toolless Mounting Buttons with Removable 90° Rotation Brackets
- G** 10 ft. Detachable Input Power Cord
- H** L6-20P Locking Input Plug
- I** Durable Metal Case
- J** LX Platform Interface
- K** RJ45 Ethernet Port
- L** RJ45 Configuration Port
- M** USB-A Port
- N** Reset Button
- O** Status LED



AC Input Connection: Insert L6-20P locking plug into compatible L6-20R utility, generator or UPS outlet. For international applications, connect user-supplied power cord with region-specific plug to C20 power inlet.

Also Includes: Configuration Cable, PDUMVROTATEBRKT, Owner's Manual



LX Platform Interface: Connect to Ethernet for remote monitoring via SNMP, Web, SSH or telnet. Add optional EnviroSense2 modules for temperature, humidity and dry contact monitoring.

Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

Specifications

Model	PDUMNV20HV2LX
Voltage	208/230V
Frequency	50/60 Hz
Maximum Capacity	20A
Agency-De-rated Capacity	16A
Input Connector	L6-20P (C20 inlet)
Cord Length	10 ft.
Outlets	20 (18 C13 / 2 C19)
Primary Mounting Option	0U (Vertical) Rackmount
Unit Weight & Dimensions (H x W x D)	6.5 lb. / 35.5 x 2.2 x 1.85 in. See next page for detailed unit measurements.
Certifications	Tested to UL 60950-1 (US & Canada), CE, NOM (Mexico), FCC & CE Class A (Emissions)

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.






- Distributes power to 20 outlets
- Java-free HTML5-based network interface allows for remote monitoring via SNMP, Web, SSH or telnet
- Displays total load in real time
- Perfect for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com





MODEL:
PDUMNV20HV2LX



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Shown with optional mounting brackets **E** and 90-degree rotation brackets **F** installed.

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.