

MODEL:

PDUMNV20HVLX

Single-Phase Monitored 0U Vertical PDU



208/230V
Single-Phase
Input/Output



24 Outlets



3.3-3.7kW



20A Max
Capacity



L6-20P
Plug



Load
Meter



Network
Interface



0U
Rack-
mount



Toolless
Mounting
Buttons




AC Inlet
Supports
International Plugs





TAA
Compliant

- A** Digital Load Meter
- B** C13 and C19 Outlets
- C** C20 Inlet
- D** Plug-Lock Insert Sleeves
- E** Removable Mounting Brackets
- F** Toolless Mounting Buttons with Removable 90° Rotation Brackets
- G** 10 ft. Detachable Input Power Cord
- H** L6-20P Twist-Lock Input Plug
- I** Durable Metal Case
- J** LX Platform Interface
- K** RJ45 Ethernet Port
- L** RJ45 Configuration Port
- M** USB-A Port
- N** Reset Button
- O** Status LED



Also includes: Configuration Cable, PDUMVROTATEBRKT, Owner's Manual




AC Input Connection: Insert L6-20P twist-lock plug into compatible L6-20R utility, generator or UPS outlet. For international applications, connect user-supplied power cord with region-specific plug to C20 power inlet.



LX Platform Interface: Connect to Ethernet for remote monitoring and individual outlet control via SNMP, Web, SSH or telnet. Add optional EnviroSense2 (E2) modules for temperature/humidity monitoring and dry contact interface.



Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.



Specifications

Model	PDUMNV20HVLX
Voltage	208/230V
Frequency	50/60 Hz
Maximum Capacity	20A
Agency-Derated Capacity	16A
Input Connector	L6-20P (inlet)
Cord Length	10 ft. / 3 m
Outlets	24 (20 C13 / 4 C19)
Primary Mounting Option	0U (Vertical) Rack Mount
Unit Dimensions (H x W x D)	70 x 2.2 x 2.7 in. / 1778 x 56 x 67 mm See next page for detailed unit measurements.
Unit Weight	8.5 lb. / 3.9 kg
Standards	Tested to UL 60950-1 (US & Canada), CE, NOM (Mexico), FCC & CE Class A (Emissions)









- Distributes power to 24 outlets
- Java-free HTML5-based network interface allows for remote monitoring and control via SNMP, Web, SSH or telnet
- Displays total load in real time
- Perfect for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com



MODEL:
PDUMNV20HVLX

TRIPP-LITE

1111 W. 35th Street
 Chicago, IL 60609 USA
 773.869.1234
 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.