SR48UBWD

SmartRack[™] Wide Rack Enclosure



48 Rack Units



3000 lb

Stationary

Load Rating



2250 lb

Rolling

Load Rating



Casters



& Side Panels



Standard

19-inch

Equipment



Mounting Slots



Adjustable Rails with **Easy-View** Depth Index



Airflow Exceeds Server OEM Requirements




Integrated Square Hole **Baying Tabs** Mounting




A Adjustable Mounting Rails

- **B** Adjustable PDU Mounting **Rails with Toolless Mounting Slots**
- Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- **E** Split Rear Doors (Lockable/Removable)
- F Side Panels (Lockable/Removable)
- **G** Heavy-Duty Casters
- Heavy-Duty Levelers
- Keys (For doors and side panels.)

Also Includes: Owner's manual, 2 stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).





- Modular design optimized for quick configuration and reconfiguration
- Ideal for rackmount server, network and telecom applications

Specifications


•	
Model	SR48UBWD
Rack Spaces	48U
Stationary Load Rating	3000 lb (1363 kg)
Rolling Load Rating	2250 lb (1022 kg)
Unit Dimensions (H x W x D)	89 x 29.53 x 43 in. (2261 x 750 x 1092 mm)
Shipping Dimensions (H x W x D)	95 x 32 x 45 in. (2413 x 813 x 1143 mm)
Unit Weight	343 lb (156 kg)
Shipping Weight	395 lb (179 kg)
Certifications	Tested to UL 60950, TIA/EIA-310-E, NOM, ROHS, CE
	(Accommodates all standard 19-inch rackmount equipment
	regardless of vendor.)
Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.	


CUL US TA SECTIONIC Industries Alliance


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com








BOTTOM VIEW

TOP VIEW



Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com