SRQ18U

SmartRack® 18U Sound Proof Server Rack





Load Capacity



750 lb. **Rolling Load** Capacity



Locking Front and Heavy-Duty



Standard 19 in. Rack Width



Adjustable



Square Hole Mounting



Foam Sound-

- A Locking Front Doors with Foam Sound-Dampening Baffles
- **B** Adjustable Mounting Rails
- Cool-Air Intakes
- Non-Removable Side Panels with Foam Sound-Dampening Baffles
- **E** Locking Rear Doors with Foam Sound-Dampening Baffles
- 6-Outlet 15A Power Strip
- **G** Brush Strip Plate
- **H** Exhaust Fans
- Hot-Air Chambers
- **K** Casters
- L Keys (for front and rear doors) Also includes: rack-mounting hardware, shipping materials and owner's manual

- Casters



Rear Doors





Mounting Rails



Dampening Baffles

FRONT VIEW BACK VIEW






Specifications	Electronic Industries Alliance
Model	SRQ18U
Rack Spaces	18U
Stationary Load Capacity	750 lb. / 340 kg
Rolling Load Capacity	750 lb. / 340 kg
Unit Dimensions (H x W x D)	38.6 x 30 x 46.7 in. / 978 x 762 x 1186 mm
Shipping Dimensions (H x W x D)	43.8 x 32 x 48.7 in. / 1112 x 812 x 1237 mm
Unit Weight	242 lb. / 109.8 kg
Shipping Weight	271 lb. / 122.9 kg
Standards	EIA/ECA-310-E; RoHS
Tripp Lite has a policy of continuous improve	ement. Specifications are subject to change without notice.

- Minimizes equipment noise by as much as 28 decibels for quieter work environment
- Floor panel intakes and built-in fans keep equipment cool to maintain top performance
- Steel/MDF cabinet locks securely to help prevent equipment damage or theft
- · Ships fully assembled for immediate deployment and equipment mounting

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com





1111 W. 35th Street Chicago, IL 60609 USA

Chicago, IL 60609 USA 773.869.1234 www.tripplite.com