

MODEL:

SR12UBFFD

SmartRack® 12U Industrial Floor Rack Enclosure



12 Rack Units



1000 lb.
Load Rating



Accommodates
Standard
19-Inch
Equipment



Dust, Drip and
Splash Protection



Heavy-Duty
Casters



Louvered Door
for Drip-Resistant
Ventilation



4 Fans for
Superior Airflow




Replaceable
Dust Filter



Square Hole
Mounting

- A** Louvered Front Door (Lockable)
- B** Dust Filter
- C** Rear Door (Lockable)
- D** Ventilation Fans
- E** Side Panels (Lockable/Removable)
- F** Adjustable Mounting Rails with Easy-View Depth Index
- G** Dust- and Drip-Resistant Cable Ports
- H** Heavy-Duty Casters (4) and Levelers (4)
- I** Keys (For Doors and Side Panels)

Also Includes: Owner's Manual and rackmount equipment mounting hardware (36 cage nuts, 36 mounting screws, 36 nylon cup washers)



- 12U floor rack enclosure cabinet for environments where networking space is limited
- Louvered front door with built-in replaceable dust filter maintains clean airflow by preventing airborne contaminants from entering the enclosure cabinet
- 4 high-performance intake fans
- 2 cable ports allow cable access while maintaining dust and moisture resistance







Specifications

Model	SR12UBFFD
Rack Spaces	12U
Equipment Mounting Depth	32.5 in. (826 mm)
Load Rating*	1000 lb. (453 kg)
Unit Dimensions (H x W x D)	25.2 x 23.6 x 38.5 in. (640 x 600 x 978 mm)
Shipping Dimensions (H x W x D)	29.8 x 27 x 41.1 in. (757 x 686 x 1044 mm)
Unit Weight	96 lb. (43.5 kg)
Shipping Weight	130 lb. (59 kg)
Standards	Meets EIA-310-E, IEC 60297-3-100, NOM (Mexico) and RoHS standards

* The load rating includes the combined weight of the unit and installed equipment. The unit must be mounted to a stable surface with user-supplied anchors capable of bearing the full load.

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

TRIPP-LITE
by **EAT·N**



Model:
SR12UBFFD

TRIPP-LITE
 by **EATON**

1111 W. 35th Street
 Chicago, IL 60609 USA
 773.869.1234
 triplite.com

Dimensions: inches [mm]
 We have a policy of continuous improvement. Specifications are subject to change without notice.
 Photos and illustrations may differ slightly from actual products.