

SmartPro 120V 1.5kVA 1.35kW Line-Interactive Sine Wave UPS, 2U, Extended Run, Network Card Options, LCD, USB, DB9

MODEL NUMBER: **SMART1500RML2UA**



Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, power surges and line noise. Ideal solution for data centers, VoIP systems and network closets.

Description

The SMART1500RML2UA SmartPro 120V 1.5kVA 1.35kW Line-Interactive Sine Wave UPS provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up servers and network storage devices, the SMART1500RML2UA switches to battery mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss. Featuring eight NEMA 5-15R outlets (four switchable) and a 10-ft. (3.05 m) power cord with 120V NEMA 5-15P input, the SMART1500RML2UA has an internal battery that provides 14 minutes of support at half load and 4.9 minutes at full load. A front-panel LCD screen lets you monitor important data, such as load level, voltage, battery charge and estimated runtimes. Adding external battery packs, such as Tripp Lite's BP36V15-2U (sold separately), provides extended runtime. Automatic voltage regulation (AVR) maintains 120V nominal output over an input range of 83V to 145V without using battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 570-joule surge suppression rating protects your equipment from harmful power surges. With Tripp Lite's PowerAlert® software (available via free download), SMART1500RML2UA enables safe unattended system shutdown and file saves in case of a prolonged power failure.

Features

Protects Mission-Critical Rack-Mounted Equipment

- Provides fully regulated sine wave AC output for servers, network storage devices and telecom hardware
- Audible alarm signals loss of utility power, overload, low battery and fault conditions
- 8 NEMA 5-15R outlets
- 10-ft. (3.05 m) power cord with 120V NEMA 5-15P input
- 0.9 power factor rating
- 570-joule surge suppression rating

Reliable Battery Backup with Expandable Runtime

- Supports half load up to 14 min. and full load up to 4.9 min.

Highlights

- Corrects under- and overvoltages from 83V to 145V
- 8 NEMA 5-15R outlets—4 switchable via network interface
- Network power management and control capability
- Expandable runtime with optional external battery packs
- 14 min. runtime at half load; 4.9 min. at full load
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

Package Includes

- SMART1500RML2UA SmartPro 120V 1.5kVA 1.35kW Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- EPO cable
- Mounting hardware
- Owner's manual

- Internal batteries designed for hot-swap field replacement
- 95% line-power efficiency rating saves money in energy costs
- Expandable runtime with optional external battery packs, such as Tripp Lite's BP36V15-2U

2 Load Banks with Switchable Outlets

- Can control 4 outlets remotely to reboot equipment or shed nonessential loads

Automatic Voltage Regulation (AVR)

- Maintains 120V nominal output over input range of 83V-145V without using battery power

EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

Interactive LCD Screen

- Front-panel LCD signals operating mode, load level, voltage, battery charge and estimated runtimes
- Rotates for easy viewing in rack-mount or tower configurations

Network Management Cards

- Compatible with Tripp Lite UPS management card options WEBCARDLX and SNMPWEBCARD

Communications Ports

- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- EPO port supports emergency shutdown in large facilities

Versatile Installation Options

- Hardware included for 4-post mounting in 2U of EIA-standard 19 in. rack
- Mounts on wall or 2-post rack with optional 2POSTRMKITWM accessory
- Mounts in upright tower position with optional 2-9USTAND accessory

Specifications

OVERVIEW	
UPC Code	037332120403
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase

VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage Correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage Correction	Input voltages between 95 and 108 are boosted by 12%
Severe Undervoltage Correction	Input voltages between 83 and 94 are boosted by 24%
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); 2-4 post front rail rackmount (UPSHDEARKIT); 4 post rackmount short-depth (4POSTRAILKITWM); Tower (2-9USTAND); Wallmount (2POSTRMKITWM);
Minimum Required Rack Depth (cm)	43.18
Minimum Required Rack Depth (inches)	17
Minimum Required Rack Depth with External Battery Pack (cm)	51
Minimum Required Rack Depth with External Battery Pack (in.)	20

Minimum Required Rack Depth without External Battery Pack (cm)	42
Minimum Required Rack Depth without External Battery Pack (in.)	16.5
Optional Mounting Accessory Notes	Optional 2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND enables upright tower UPS placement; 2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM enables wall-mount and 2-post rackmount installation; 4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary UPS Depth (mm)	342
Primary UPS Height (mm)	88
Primary UPS Width (mm)	439
Shipping Dimensions (hwd / in.)	8.80 x 23.00 x 19.30
Shipping Dimensions (hwd / cm)	22.35 x 58.42 x 49.02
Shipping Weight (lbs.)	53.53
Shipping Weight (kg)	24.28
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.76 x 43.94 x 34.16
UPS Power Module Dimensions (hwd, in.)	3.45 x 17.3 x 13.45
UPS Power Module Weight (kg)	21.09
UPS Power Module Weight (lbs.)	46.5
Unit Weight (lbs.)	46.5000
Unit Weight (kg)	21.09
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	237
Battery Mode BTU / Hr. (Full Load)	751
AC Mode Efficiency Rating (100% Load)	95%
Audible Noise	45 dBA maximum, front side 1m
COMMUNICATIONS	
Network Management Cards	Web-Management-Accessory-Card~WEBCARDLX ; SNMPWEBCARD

Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports , download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management card optional
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	4 milliseconds (AC to battery mode), 1 millisecond (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
Grounding Lug	Back panel grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance