



S3M20K-NIB Estimated Runtime

| UPS Model | Battery Pack Model | Battery Pack Qty | Load in Kilowatts (kW) | | | | | | | | | |
|------------|--------------------|------------------|------------------------|-----|-----|-----|------|------|------|------|------|------|
| | | | 2kW | 4kW | 6kW | 8kW | 10kW | 12kW | 14kW | 16kW | 18kW | 20kW |
| S3M20K-NIB | BP240V09 | 1 | 209 | 93 | 56 | 39 | 29 | 23 | 19 | 16 | 13 | 12 |
| S3M20K-NIB | BP240V09 | 2 | 454 | 211 | 131 | 93 | 71 | 56 | 46 | 39 | 33 | 29 |
| S3M20K-NIB | BP240V09K | 1 | 209 | 93 | 56 | 39 | 29 | 23 | 19 | 16 | 13 | 12 |
| S3M20K-NIB | BP240V09K | 2 | 454 | 211 | 131 | 93 | 71 | 56 | 46 | 39 | 33 | 29 |
| S3M20K-NIB | BP240V40 | 1 | 236 | 105 | 64 | 45 | 34 | 26 | 22 | 18 | 15 | 13 |
| S3M20K-NIB | BP240V40 | 2 | 509 | 238 | 149 | 106 | 80 | 64 | 53 | 44 | 38 | 33 |
| S3M20K-NIB | BP240V40 | 3 | 781 | 375 | 239 | 171 | 132 | 105 | 87 | 74 | 64 | 56 |
| S3M20K-NIB | BP240V40L | 1 | 509 | 238 | 149 | 106 | 80 | 64 | 53 | 44 | 38 | 33 |
| S3M20K-NIB | BP240V40L | 2 | 1,049 | 513 | 330 | 239 | 185 | 149 | 123 | 105 | 91 | 80 |
| S3M20K-NIB | BP240V40L | 3 | 1,571 | 787 | 514 | 377 | 294 | 238 | 199 | 170 | 148 | 130 |
| S3M20K-NIB | BP240V65 | 1 | 406 | 187 | 116 | 82 | 62 | 49 | 40 | 34 | 29 | 25 |
| S3M20K-NIB | BP240V65 | 2 | 849 | 410 | 261 | 188 | 145 | 116 | 96 | 81 | 70 | 61 |
| S3M20K-NIB | BP240V65 | 3 | 1,280 | 633 | 411 | 299 | 232 | 188 | 156 | 133 | 115 | 101 |
| S3M20K-NIB | BP240V65L | 1 | 849 | 410 | 261 | 188 | 145 | 116 | 96 | 81 | 70 | 61 |
| S3M20K-NIB | BP240V65L | 2 | 1,698 | 855 | 560 | 411 | 322 | 261 | 218 | 187 | 162 | 143 |
| S3M20K-NIB | BP240V100 | 1 | 646 | 306 | 193 | 138 | 106 | 84 | 70 | 59 | 51 | 44 |

All runtime values are shown in minutes.