



S3M40KX-NIB Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2.5kW	5kW	7.5kW	10kW	12kW	14kW	16kW	18kW	21kW	24kW	27kW	30kW	33kW	36kW
S3M40KX-NIB	BP480V40	1	361	171	107	76	61	50	42	37	30	25	22	19	17	15
S3M40KX-NIB	BP480V40	2	760	376	242	175	141	118	100	87	72	61	53	46	41	37
S3M40KX-NIB	BP480V40	3	1,150	583	381	278	227	190	163	142	118	101	87	77	68	61
S3M40KX-NIB	BP480V40	4	1,530	788	520	383	314	265	228	199	167	143	124	109	97	88
S3M40KX-NIB	BP480V200	1	511	247	156	112	90	75	63	55	45	38	33	29	25	23
S3M40KX-NIB	BP480V200	2	1,053	531	346	252	205	172	147	128	107	91	79	69	61	55
S3M40KX-NIB	BP480V200	3	1,577	814	538	396	325	274	236	206	173	148	129	113	101	91
S3M40KX-NIB	BP480V200	4	2,080	1,092	729	541	446	378	327	287	241	207	181	160	143	129
S3M40KX-NIB	BP480V65	1	611	298	190	137	110	92	78	67	56	47	41	36	31	28
S3M40KX-NIB	BP480V65	2	1,246	634	416	304	249	209	179	156	130	111	96	85	76	68
S3M40KX-NIB	BP480V65	3	1,854	966	642	476	391	331	285	250	210	180	157	139	124	112
S3M40KX-NIB	BP480V65	4	2,434	1,291	867	647	534	454	393	345	291	251	219	194	174	157
S3M40KX-NIB	BP480V300	1	740	365	235	169	137	114	97	84	70	59	51	45	40	36
S3M40KX-NIB	BP480V300	2	1,492	768	506	373	305	257	221	193	162	138	120	106	94	85
S3M40KX-NIB	BP480V300	3	2,205	1,162	777	578	477	404	350	307	259	222	194	172	154	139
S3M40KX-NIB	BP480V300	4	2,880	1,545	1,044	782	649	552	479	422	357	308	270	240	215	195
S3M40KX-NIB	BP480V100	1	956	479	311	226	184	154	131	114	95	81	70	61	54	49
S3M40KX-NIB	BP480V100	2	1,899	991	660	489	402	340	294	257	216	185	162	143	128	115
S3M40KX-NIB	BP480V100	3	2,778	1,487	1,004	751	622	529	459	405	342	295	258	229	206	186
S3M40KX-NIB	BP480V100	4	3,598	1,965	1,340	1,010	841	718	625	552	469	406	357	318	286	259

All runtime values are shown in minutes.